



Representative Image

## Catalog No. TH4361

Description: 30A 3P HD N1 600V FUSIBLE SW

UPC No 783164492088

Home > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Disconnect & Safety Switches
GO Schedule	S1

### Specifications

Amperage	30 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	12-2
240 Vac, Time Delay, 1-ph	7,5 hp
480 Vac, NEC Std, 1-ph	3 hp
480 Vac, NEC Std, 3-ph	5 hp
480 Vac, Time Delay, 1-ph	7,5 hp
480 Vac, Time Delay, 3-ph	15 hp
600 Vac, NEC Std, 1-ph	3 hp
600 Vac, NEC Std, 3-ph	7,5 hp
600 Vac, Time Delay, 1-ph	10 hp
600 Vac, Time Delay, 3-ph	20 hp
125 Vdc	3 hp
250 Vdc	5 hp

### Classifications

CSA Certified	Yes
UL Listed	Yes

### Dimensions

Height	12,6 in
--------	---------

## Dimensions

Depth	4 in
Width	8,3 in
Weight	11 lb

## Publications

Title	Publication No.	Publication Type
<a href="#">Let's be clear</a>		
Enhancements to Safety Switches: Clear line shield; bright red switches and factory installed neutrals	SSPostcard	Ads
<a href="#">60A</a>		
1 page outline drawing in .pdf format.	10103091SH102	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.