

DESCRIPTION

The I-420-EM-R from IOTA Engineering is a UL Listed fluorescent emergency ballast that allows the same fixture to be used for both normal and emergency operation. In the event of a power failure, the I-420-EM-R switches to the emergency mode and operates one or two of the existing lamps for 90 minutes. The unit contains a battery, charger, and inverter circuit in a single can. The I-420-EM-R can be used with most 10W-57W twin, triple, quad tube, 2D and Straight 4-pin compact fluorescent lamps, with an initial output of up to 1100 lumens for one or two lamps. The I-420-EM-R utilizes AC output to ensure compatibility with new lamp technologies, and features lamp selector leads for optimizing light output for designated lamp types. The I-420-EM-R is provided with flex for wiring to the fixture or ballast compartment. A single-piece test switch and charge indicator is provided with all necessary hardware for installation within the downlight reflector. The I-420-EM-R is suitable for use in damp locations.


SPECIFICATIONS


Input Voltage	(Dual) 120/277V, 60Hz
Input Wattage	
Lamps Operated	
Emergency Operation	(1) 10W-57W or (2) 10W-26W 90 minutes
Initial Illumination	
Operating Temp	
Battery	24 Hour Recharge 7-10 Year Life Expectancy
Weight	5.4 lbs.
Approval	UL and CUL Listed



DIMENSIONS

13.3" x 2.4" x 1.5" (mounting center 12.75")





MODEL NO:	
TYPE:	
PROJECT:	
COMMENTS:	

1100 Lumens

LAMPS OPERATED*



- (1) 10W-57W 4-PIN Compact
- (2) 10W-26W 4-PIN Compact



Select LED Retrofit Tubes

*Refer to Lumen Reference Chart and LED Retrofit Reference Chart for list of compatible lamps.

PRODUCT ADVANTAGES

- AC output for compatibility with Low-Mercury Content Amalgam lamps
- Time Delay feature for compatibility with End-of-Lamp-Life Circuitry
- Open Circuit Isolation protects unit when load is absent
- Reflector-mount single-piece test switch and charge indicator

FEATURES

- Will cold start and operate all specified lamps
- Long life high temperature recyclable Ni-Cad battery
- Galvanized steel case
- Includes one-piece reflector-mount TBTS test switch and charge indicator
- For use with switched or unswitched fixtures
- 5-Year Warranty. See Warranty Page for details.
- Lamp selector leads optimize light output for designated lamp type
- Rated for use in damp locations and plenum fixtures.
- Meets or exceeds all NEC, IBC, and Life Safety Code Emergency Lighting Requirements
- RoHS Compliant
- International Voltage Models available



I-420-FM-R

FLUORESCENT EMERGENCY BALLAST FOR 4-PIN LAMPS

OPTIONS

TEST KIT CONFIGURATION

 LIGHTED TEST SWITCH IN REFLECTOR RECOMMENDED FOR OEM INSTALLATION ONLY.
CONTACT CUSTOMER SERVICE FOR DETAILS.

MOUNTING CONFIGURATION

- O -R (Dual Flex)
- -R-J (Junction Box Mount with Single Flex)

VOLTAGE RATINGS

- 120/277V 60HZ (STANDARD)
- O 220V 50HZ
- O 240V 60HZ
- O 120V 50HZ

INITIAL LUMEN RATINGS

LAMP	1 LAMP	2 LAMPS
13W PL CF 4-PIN	570	900
18W PL CF QUAD 4-PIN	680	1010
26W PL CF QUAD 4-PIN	810	1200
32W PL CF QUAD 4-PIN	910	
42W PL CF QUAD 4-PIN	1040	
57W PL CF QUAD 4-PIN	1180	

LED Retrofit Tube Options

This IOTA Emergency Ballast is UL Listed for emergency operation of select LED retrofit tube applications. For a complete list of acceptable LED retrofit tube options, refer to the IOTA LED Retrofit Tube Reference Chart at www.iotaengineering.com/IOTA-LED-Retrofit.pdf

REMOTE MOUNTING

When battery packs are remote mounted, consult Customer Service for the maximum allowable distance between the battery pack and lamp(s).

I-420-EM-R SAMPLE SPECIFICATION

Emergency lighting shall be provided by using a standard fluorescent fixture equipped with an IOTA I-420-EM-R fluorescent emergency battery pack. The I-420-EM-R shall consist of a high temperature, maintenance-free nickel cadmium battery, charger board and an electronic circuit enclosed in a 13.3" x 2.4" x 1.5" vandal-resistant galvanized steel case. The unit is designed for installation on top of the fixture and is equipped with 1/2" flex for wiring to the fixture or ballast compartment. A combination one-piece long-life LED charge indicator light and test switch shall be included for installation directly within the reflector. The fluorescent EM pack shall operate one 10W-57W or two 10W-26W twin, triple, quad tube, 2D or straight 4-pin fluorescent lamps. The I-420-EM-R shall provide reduced illumination for a minimum of 90 minutes in the emergency mode with a total initial output of 1100 lumens. The I-420-EM-R will operate the lamp with AC output and will feature lamp selector leads for optimizing light output for the designated lamp type. The I-420-EM-R shall have 4 watts of input power and a battery capacity of 24 watt hours. The I-420-EM-R is UL Listed and meets or exceeds all NEC and Life Safety Code Emergency Lighting Requirements, and rated for us in damp locations. The I-420-EM-R is warranted for a full five (5) years from the date of purchase.