



## SolarEdge Power Optimizer

Module Add-On for Commercial Installations  
for North America P600 / P700 / P730 /  
P800p / P800s



POWER OPTIMIZER

### PV power optimization at the module-level The most cost effective solution for commercial and large field installations

- Specifically designed to work with SolarEdge inverters
- Up to 25% more energy
- Superior efficiency (99.5%)
- Balance of System cost reduction; 50% less cables, fuses and combiner boxes, over 2x longer string lengths possible
- Fast installation with a single bolt
- Advanced maintenance with module-level monitoring
- Module-level voltage shutdown for installer and firefighter safety
- Use with two PV modules connected in series or in parallel



# SolarEdge Power Optimizer Module Add-On For Commercial Installations for North America P600 / P700 / P730 / P800p / P800s

	P600 (for 2 x 60-cell PV modules)	P700 (for 2 x 72-cell PV modules)	P730 (for 2 x high power 72-cell PV modules)	P800p (for parallel connection of 2x 96-cell 5" PV modules)	P800s (for series connection of 2x high power or bi-facial modules)	
<b>INPUT</b>						
Rated Input DC Power <sup>(1)</sup>	600	700	730	800		W
Absolute Maximum Input Voltage (Voc at lowest temperature)	96	125		83	120	Vdc
MPPT Operating Range	12.5 - 80	12.5 - 105		12.5 - 83	12.5 - 105	Vdc
Maximum Short Circuit Current (Isc)	10.1		11	14	12.5	Adc
Maximum DC Input Current	12.65		13.75	17.5	15.63	Adc
Maximum Efficiency				99.5		%
Weighted Efficiency				98.6		%
Overvoltage Category				II		
<b>OUTPUT DURING OPERATION (POWER OPTIMIZER CONNECTED TO OPERATING SOLAREEDGE INVERTER)</b>						
Maximum Output Current	15			18		Adc
Maximum Output Voltage				85		Vdc
<b>OUTPUT DURING STANDBY (POWER OPTIMIZER DISCONNECTED FROM SOLAREEDGE INVERTER OR SOLAREEDGE INVERTER OFF)</b>						
Safety Output Voltage per Power Optimizer				1		Vdc
<b>STANDARD COMPLIANCE</b>						
EMC	FCC Part15 Class B, IEC61000-6-2, IEC61000-6-3					
Safety	IEC62109-1 (class II safety), UL1741					
Material	UL-94 (5-VA), UV Resistant					
RoHS	Yes					
<b>INSTALLATION SPECIFICATIONS</b>						
Compatible SolarEdge Inverters	Three phase inverters					Vdc
Maximum Allowed System Voltage	1000					
Dimensions (W x L x H)	128 x 152 x 43 / 5 x 5.97 x 1.69	128 x 152 x 50 / 5 x 5.97 x 1.96		128 x 152 x 50 / 5 x 5.97 x 1.93		mm / in
Weight (including cables)	994 / 2.2	1064 / 2.34		1090 / 2.4	1064 / 2.34	gr / lb
Input Connector	MC4 Compatible			MC4 Compatible (Single or Dual input) <sup>(4)</sup>	MC4 Compatible	
Output Wire Type / Connector	Double Insulated; MC4 Compatible					
Output Wire Length	1.8 / 5.9	2.1 / 6.9		1.8 / 5.9	2.1 / 6.9	m / ft
Operating Temperature Range <sup>(2)</sup>	-40 - +85 / -40 - +185					°C / °F
Protection Rating	IP68 / NEMA6P					
Relative Humidity	0 - 100					%

<sup>(1)</sup> Rated STC power of the module. Module of up to +5% power tolerance allowed.

<sup>(2)</sup> For ambient temperature above +70°C / +158°F power de-rating is applied. Refer to Power Optimizers Temperature De-Rating Application Note for more details.

PV SYSTEM DESIGN USING A SOLAREEDGE INVERTER <sup>(3)(4)</sup>		THREE PHASE 208V		THREE PHASE 480V		
Compatible Power Optimizers		P600, P700 & P730 <sup>(5)</sup>	P800 <sup>(5)</sup>	P600, P700 & P730	P800	
Minimum String Length	Power Optimizers	8		13		
	PV Modules	16		26		
Maximum String Length	Power Optimizers	30		30		
	PV Modules	60		60		
Maximum Power per String		6000 <sup>(6)</sup>	7200	12750 <sup>(7)</sup>	15300	W
Parallel Strings of Different Lengths or Orientations		Yes				

<sup>(3)</sup> P600, P700 and P730 can be mixed in one string. It is not allowed to mix P600/P700/P730/P800 with P300/P320/P400/P405 in one string.

<sup>(4)</sup> In a case of odd number of PV modules in one string it is allowed to install one P600/P700 /P800 power optimizer connected to one PV module. When connecting a single module to the P800p the single input version should be used.

<sup>(5)</sup> P700/P730/ P800 design with three phase 208V inverters is limited. Use the SolarEdge Site Designer for verification.

<sup>(6)</sup> For SE14.4KUS: It is allowed to install up to 6,500W per string when 3 strings are connected to the inverter and when the maximum power difference between the strings is up to 1,000W.

<sup>(7)</sup> For SE33.3KUS: It is allowed to install up to 15,000W per string when 3 strings are connected to the inverter and when the maximum power difference between the strings is up to 2,000W.

