



GE
Lighting

43233 - GE LED R20

LED7DR20/830

- Using only 7 watts of energy, save over \$99 in energy cost over the rated life of a lamp versus a standard 45-watt incandescent lamp based on \$0.11 per kWh
- Energy efficiency and long life mean fewer lamp replacements versus standard incandescent and halogen light sources
- These lamps are energy efficient, contain no lead or mercury, and are compliant with material restriction requirements of RoHS
- Halogen-like color

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Body Color	White
Dimmable	Yes
Lamp Type	LED-R
Product Color	White
Product Technology	LED
Rated Life (Hours)	25000 h
Dimmable / Non-Dimmable	Yes
10 Digit U	4316843233
Lamp Count	1
Life in Years	22.8 yr
Replacement Watts	45 W
Requested Structure	Carton
Estimated Energy Cost per Year	0.84
Base	E26
Bulb Shape	R20

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	67.1
Initial Lumens-nominal	470 lm
Color Rendering Index-CRI	80
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	43233
Description	LED7DR20/830
Alternative Unit Of Measure	CASE
Standard Package Quantity	6
Ean UPC	043168432337
Standard Package GTIN	10043168432334
No Of Items Per Sales Unit	
No Of Items Per Standard Package	6
Sales Unit	Case
UCC	043168432337
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168432337
Standard Package GTIN	00043168432337
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168432337

DIMENSIONS

Bulb Max Overall Length-MOL	3.64 in
-----------------------------	---------

ELECTRICAL CHARACTERISTICS

Voltage <Nom>	120 V
Input Voltage [nom]	120 V
Rated power (Watts)	7 W

CAUTIONS & WARNINGS

Caution

Risk of Electric Shock

Suitable for damp locations

Not for use in totally enclosed luminaires

Not intended for use with emergency exit fixtures or emergency exit lights

Performance may vary with electronic timers / photocells or dimmers

