



# 2' LED Strip Light

1800 lms | 120-277VAC | Model 54260144 | Part ST-2-20-840-MV-N

- > Energy Saving 10Watt Integrated LED
- > Uses 87% Less Energy than Equivalent 34 Watt Incandescent Bulb
- > Cool White 4000K CCT
- > Lasts 45 years or 50,000 Hours Continuous Use
- > Maintenance Free — No Bulb Replacements
- > 5 Year Limited Warranty
- > Suitable for use in closets, as defined in NEC® Section 410.16 (C)



## SPECIFICATIONS

Model	54260144
Part	ST-2-20-840-MV-N
Description	2' LED Strip Light
Input Voltage (VAC)	120-277
Wattage	14
Dimmability	Non-Dimmable
Average Rated Life <sup>1</sup>	50,000 hours
Typical Lumens <sup>2</sup>	1800
CCT <sup>3</sup>	4000K
Location Rating	UL Damp
CRI <sup>4</sup>	≥80
Beam Angle	107
Operating Temperature	Min -4°F (-20° C), Max 95°F (35° C)
Power Factor	>0.9
R9	15
DUV	-0.0002
CBCP	296
Operating Frequency (Hz)	50/60Hz

- 1 Hours lifetime with 70% lumen maintenance
- 2 Thermally stable typical lumens (±10%)
- 3 Thermally stable CCT (±10%)
- 4 Color rendering index/Ra

**TO ORDER:**  
[www.ETiSSL.com](http://www.ETiSSL.com)  
Call: 1.855.ETi.SSLI  
1.855.384.7754

**LED lighting facts**  
A Program of the U.S. DOE

Light Output (Lumens)	1800
Watts	20
Lumens per Watt (Efficacy)	90
Color Accuracy Color Rendering Index (CRI)	80
Light Color Correlated Color Temperature (CCT)	4000 (Bright White)

2700K 3000K 4500K 6500K

Warm White Bright White Daylight

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit [www.lightingfacts.com](http://www.lightingfacts.com) for the Label Reference Guide.

Registration Number: SBAM-5E3EK3 (9/22/2017)  
Model Number: 542601##/##-41-50  
Type: Luminaire - Linear





# 2' LED Strip Light

1800 lms | 120-277VAC | Model 54260144 | Part ST-2-20-840-MV-N

## SHIPPING INFORMATION

Model	54260144
Part	ST-2-20-840-MV-N
UPC	849489002682
Product Dimensions (L x W x H in.)	24.02 x 2.2 x 3.9
Product Dimensions (L x W x H cm.)	61 x 5.6 x 7
Product Weight (lbs.)	1.4
Inner Carton Quantity	N/A
Inner Carton Bar Code	N/A
Inner Carton Dimensions (L x W x H in.)	N/A
Inner Carton Dimensions (L x W x H cm.)	N/A
Inner Carton Weight (lbs)	N/A
Master Carton Quantity	6
Master Carton Bar Code	50849489002687
Master Carton Dimensions (L x W x H in.)	25.31 x 7.68 x 7.68
Master Carton Dimensions (L x W x H cm.)	64.3 x 19.5 x 19.5
Master Carton Weight (lbs)	12.41
Pallet Quantity	252

## COMPATIBILITY

Dimmers: N/A

Sensors: N/A

## AVAILABLE ACCESSORIES

Model	Part	Description	Wattage	Input Voltage	Case Pack
N/A	N/A	N/A	N/A	N/A	N/A

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, Please see [www.fcc.gov](http://www.fcc.gov)

**TO ORDER:**  
[www.ETiSSL.com](http://www.ETiSSL.com)  
Call: 1.855.ETi.SSLI  
1.855.384.7754

ETi Solid State Lighting, Inc.  
720 Corporate Woods Parkway  
Vernon Hills, IL 60061  
Phone: 855.384.7754  
Fax: 847.383.6256