




# LED Panel

## F-L24/50/840/D/HE-79

2' x 4' - LED High Efficiency Panel

- Mercury free
- 0-10V Dimmable
- 45% Energy savings compared to fluorescents
- 4-Lamp 32WT8 equivalent



<b>Item #</b>	F-L24/50/840/D/HE-79
<b>Product Code</b>	73351
<b>UPC Code</b>	751338003323
<b>Watts</b>	50
<b>Volts</b>	120-277VAC, 50/60Hz
<b>Frame</b>	White (T-bar)
<b>CRI</b>	80
<b>Color Temp</b>	4000K
<b>Initial Lumens</b>	6,500
<b>Beam Angle</b>	150°
<b>Efficacy, Lm/watt</b>	130
<b>Average Rated Life</b>	50,000 L70
<b>Ambient Temp Rating</b>	-20°C to 45°C
<b>Weight (lbs)</b>	24
<b>Warranty</b>	5 years

Specifications are subject to change without prior notice.



### Optional Frame

Item #: F-L2X4-FRAME

Product Code: 78631



[www.topaz-usa.com](http://www.topaz-usa.com)

NY Office: 925 Waverly Ave • Holtsville, NY 11742 • 800-666-2852 • Fax: 631-758-8026

CA Office: 225 Parkside Drive, San Fernando, CA 91340 • 888-551-2852 or 818-838-3123 • Fax: 888-690-2852 or 818-838-3102

FL Office: 2020 West 26th Street, Jacksonville, FL 32209 • 800-338-2852 • Fax: 772-778-5386