

### APPLICATIONS

The HBP High Bay is the lighting solution for a wide variety of applications. The ideal solution for industrial, commercial and other high bay applications.

### FEATURES & BENEFITS

- ◆ Full steel body for excellent rigidity
- ◆  $L_{70}$  life > 54,000 hrs;  $L_{90}$ =36,000 hrs
- ◆ Frosted lens
- ◆ Hanging chains are included
- ◆ 0-10V Dimmable
- ◆ Long life, high efficiency
- ◆ 10' 16/3 SJOT black cord included
- ◆ 23.6" x 12.59" x 3.54"
- ◆ Operating temperature -20°C to +45°C -non condensing
- ◆  $c_{UL_{US}}$  Listed




### ORDERING DATA

EXAMPLE: HBP24-LED105FRDMV50

HBP	24	LED	105	FR	DMV	50	
Series	Size	Gear	Wattage & Lumens	Lens	Driver	Color Temp	
HBP	24 24"	LED	105 105 Watts 14131 Lumens	FR Frosted	DMV 120-277VAC 0-10V Dimmable	50 5000K	
							Options
							A-HBP24WG wire guard with clips

### Dimensions



**DLC Premium**  
HBP24-LED105FRDMV50

Dimensions and specifications subject to change without notice.



◆ 800-444-WATT ◆ www.mobern.com ◆  
8200 Stayton Dr., Ste. 500, Jessup, MD 20794

CAT#

JOB NAME

TYPE