
STAINLESS STEEL CONDUIT





PRODUCT DETAILS

Material:

316 SS and 304 SS

Standards:

ASTM A312

Country of Origin:

Manufactured in USA

UL File Number:


DYWV.E300683 (Standard 6A)

Canada UL File Number:

DYWV7.E300683 (Standard 6A)



- Rigid/Heavywall, Schedule 40
- · Provides a means of protection for wiring and cable in electrical systems
- · Threaded on both ends, NPT
- Offered in Type 316 SS and Type 304 SS
- · Supplied complete with one coupling and a color-coded thread protector for opposite end
- Stocked in 10' lengths; custom lengths can be made available upon request
- Manufactured in stainless steel to help prevent corrosion
- Can be installed using ordinary hand tools and require little maintenance or repair
- Provided in a bright, polished finish that does not require touch up or painting



*shown without coupling

Part Number	Size	Weight/ Stick (lbs.)	D]HW (Threads per Inch)	Length w/o Coupling "A" (ft.)	Outside Diameter "B" (in.)	Wall Thickness "C" f]b'Ł	Inside Diameter "D" f]b'Ł
CND50	½ in.	8	14	9-11-¼	0.84	0.11	0.62
CND75	¾ in.	11	14	9-11-¼	1.05	0.11	0.82
CND100	1 in.	16	11-1/2	9-11	1.32	0.13	1.05
CND125	1¼ in.	22	11-1/2	9-11	1.66	0.14	1.38
CND150	1½ in.	26	11-1/2	9-11	1.90	0.15	1.61
CND200	2 in.	35	11-1/2	9-11	2.38	0.15	2.07
CND250	2½ in.	55	8	9-10-1/2	2.88	0.20	2.47
CND300	3 in.	72	8	9-10-1/2	3.50	0.22	3.07
CND400	4 in.	100	8	9-10-¼	4.50	0.24	4.03

Type 316 SS part numbers listed above; Type 304 SS products are denoted by adding "-304SS." For example: CND75-304SS

