MonoRail Mini-Surface Transformer 250w EL LED



DESCRIPTION

Truly minimalist design with the industry's smallest 250 watt surface transformer. Compatible with both LED and Halogen lamped 12v low-voltage pendants and heads. Now protected by a 5-year warranty. Constructed of die-cast aluminum. Mounts to a standard 4" ceiling junction box with round plaster ring (provided by electrician). Can be used with 2" or greater Standoffs and a Power Extender - Search for accessories on techlighting.com or consult the Tech Lighting Systems Ordering Guide for details.









monorail minisurface transformer-250w el -satin nickel

shown with monorail

monorail minisurface transformer-250w el - antique bronze

ORDERING INFORMATION

700MOMRT250E FINISH

VOLTAGE

Z- ANTIQUE BRONZE LED

S- SATIN NICKEL LED 120V IN/12V OUT

LED

As a general rule when using LED fixtures we do not recommend using greater than 70% of specified maximum wattage on the transformer due to inrush current. for assistance, please contact our technical support department.



7400 Linder Avenue Skokie, Illinois 60077 T 847.410.4400 F 847.410.4500

Tech Lighting, L.L.C.

700MOMRT250E	
FIXTURE TYPE:	
JOB NAME:	
NOTES:	



©2018 Tech Lighting, L.L.C. All Rights Reserved. The "Tech Lighting" graphic is a registered trademark of Tech Lighting, L.L.C. are Tech Lighting reserves the right to change specifications for product improvements without notification.