



**Color:** White

**UPC Code:** 078477675281

**Country Of Origin:** Mexico

## T5362-W

Duplex Receptacle Outlet, Heavy-Duty Industrial Specification Grade, Tamper-Resistant, Smooth Face, 20 Amp, 125 Volt, Back or Side Wire, NEMA 5-20R, 2-Pole, 3-Wire, Self-Grounding - White

### Technical Information

#### Warranty

**Horsepower Rating:** 1 HP

**Product Warranty:** 10 Years

#### AC Horsepower Rating

**Amperage:** 20 A

**Dielectric Voltage:** Withstands 3000 V minimum

**Grounding:** Self-Grounding

**Horsepower Rating:** 1 HP

**Pole:** 2

**Temperature Rise:** Max 30 °C after 250 cycles OL at 200 percent rated current

**Voltage:** 125 VAC

**Wire:** 3

#### Electrical Specifications

**Amperage:** 20 A

**Dielectric Voltage:** Withstands 3000 V minimum

**Flammability:** Rated V-0 per UL 94

**Grounding:** Self-Grounding

**Operating Temperature:** -40°C to 75°C

**Pole:** 2

**Temperature Rise:** Max 30 °C after 250 cycles OL at 200 percent rated current

**Voltage:** 125 VAC

**Wire:** 3

#### Environmental Specifications

**Body Material:** PBT Polyester Blend

**Face Material:** PBT Polyester Blend

**Flammability:** Rated V-0 per UL 94

**Ground Clips:** Brass

**Ground Contacts:** 0.030" Brass

**Grounding Screw:** #8 hex head, triple drive Brass

**Line Contacts:** 0.030" Phosphor Bronze

**Mounting Screws:** Triple-Drive Plated Steel

**Operating Temperature:** -40°C to 75°C

**Strap Material:** Steel

**Terminal Clamps:** Brass

**Terminal Screws:** #8 Triple-Drive Brass

#### Material Specifications

**Body Material:** PBT Polyester Blend

**Face Material:** PBT Polyester Blend

**Ground Clips:** Brass

**Ground Contacts:** 0.030" Brass

**Grounding Screw:** #8 hex head, triple drive Brass

**Line Contacts:** 0.030" Phosphor Bronze

**Mounting Screws:** Triple-Drive Plated Steel

**Product ID:** Ratings are permanently marked on device

**Strap Material:** Steel

**Terminal Accom.:** #14 AWG - #10 AWG

**Terminal Clamps:** Brass

**Terminal ID:** Brass - Hot, Green - Ground, Silver - Neutral

**Terminal Screws:** #8 Triple-Drive Brass

**Termination:** Back or Side Wire

**Wire Type:** Stranded or Solid

#### Mechanical Specifications

**Color:** White

**Color / Feature:** White

**Device Type:** Duplex Receptacle Outlet

**Grade:** Heavy-Duty Industrial Specification Grade

**Product ID:** Ratings are permanently marked on device

**Terminal Accom.:** #14 AWG - #10 AWG

**Terminal ID:** Brass - Hot, Green - Ground, Silver - Neutral

**Termination:** Back or Side Wire

**Wire Type:** Stranded or Solid

#### Product Features

**ANSI:** C-73

**Applicable Standards:** UL 498, Fed Spec W-C-596, CSA C22.2. No. 42

**Certification/Listing:** cULus, NOM-ANCE

**Color:** White

**Color / Feature:** White

**Device Type:** Duplex Receptacle Outlet

**Feature:** Tamper-Resistant, Smooth Face

**Grade:** Heavy-Duty Industrial Specification Grade

**RoHS:** RoHS Compliant

#### Standards & Certifications

**ANSI:** C-73

**Applicable Standards:** UL 498, Fed Spec W-C-596, CSA C22.2. No. 42


**Certification/Listing:** cULus, NOM-

ANCE  
**RoHS:** RoHS Compliant

**Patents\***

CA2483480	US6743029
CA2621644	US7355117
CA2624409	US7820909
CA2677283	US7868719
CN200880004760.2	US8242362
MX257790	US8684771
MX321216	

\*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.



**SPECIFICATION SUBMITTAL**

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

