


Siemens Low Voltage Residential Generators Standby Power (Generators) - Generators: Accessories are Residential Enclosures Standby Power (Generators). Sub Brand: Standby Power Systems Type: Manual Transfer Interlock Kit Application: For use on load centers or meter combinations that will accept 2-pole circuit breakers opposite one another Standard: UL/NEMA 1/3R Amperage Rating: 225A Mounting: Flush or Surface Length: 3.6 Width: 5.1 Height: 12.9



Mounting type	Flush or Surface
Suitability for operation	For use on load centers or meter combinations that will accept 2-pole circuit breakers opposite one another
Electricity	
Current at AC rated value	225 A
Model	
product brandname	Siemens
Product sub brand name	Standby Power Systems
Product type designation	Manual Transfer Interlock Kit
Mechanical Design	
Depth [in]	3.6 in
Height [in]	12.9 in
Width [in]	5.1 in
General product approval	
Certificate of suitability	UL/NEMA 1/3R
last modified:	08/20/2017