

**EASY-WRAP™**  
**Electrical Tape**  
 Premium 070 & 085  
 EWP Series




**SPECIFICATIONS**

- UL Listed and CSA.
- **Temperature Rating:** Suitable for use at no more than 600V and not more than 80 °C (176 °F).
- **CSA Temperature Range:** -18 °C to 105 °C (-0.4 °F to 221 °F).
- Meets MIL-I-24391C, HH-I-595C and ASTM D-3005 (Premium 085).

**FEATURES**

- 7 mil., all-weather, premium grade, pressure sensitive vinyl electrical tape (Premium 070).
- Available in standard black and nine assorted colors for easy identification or color coding (Premium 070).
- Cold and sunlight resistant.
- Flame retardant.
- Suitable for use in all kinds of electrical and mechanical applications.
- Provides exceptional flexibility and performance over a wide range of temperatures.
- \*8.5 mil., all-weather, premium grade, pressure sensitive vinyl electrical tape (Premium 085).
- \*Available in standard black (Premium 085).



CAT. NO.	FIG. NO.	COLOR	LENGTH (FT.)	WIDTH (IN.)	THICKNESS (IN.)	STD. CTN. QTY.
EWP7066	1	Black	66	0.75	0.007	10
EWP7066-1	2	Brown	66	0.75	0.007	10
EWP7066-2	3	Red	66	0.75	0.007	10
EWP7066-3	4	Orange	66	0.75	0.007	10
EWP7066-4	5	Yellow	66	0.75	0.007	10
EWP7066-5	6	Green	66	0.75	0.007	10
EWP7066-6	7	Blue	66	0.75	0.007	10
EWP7066-7	8	Purple	66	0.75	0.007	10
EWP7066-8	9	Grey	66	0.75	0.007	10
EWP7066-9	10	White	66	0.75	0.007	10
*EWP8566	11	Black	66	0.75	0.0085	10