

6220UL Multi-Conductor - Commercial Applications - 2 Conductors Cabled



For more Information
please call

1-800-Belden1

**General Description:**

Fire Alarm Cable, Plenum-FPLP, 2-16 AWG solid bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

Usage (Overall)

Suitable Applications: Fire Protection, Alarm, Signal, Monitor/Detection, Audio Circuits, Control Circuits, Initiating Circuits, Notification Circuits

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	16	Solid	BC - Bare Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.008

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	.015

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)	Twists (twist/ft)
2.75	4.4

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 0.166 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	0°C To +75°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	23.500 lbs/1000 ft.
Max. Recommended Pulling Tension:	62.400 lbs.
Min. Bend Radius/Minor Axis:	1.625 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	FPLP
NEC Articles:	760
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes

ENGLISH MEASUREMENT VERSION

6220UL Multi-Conductor - Commercial Applications - 2 Conductors Cabled

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Other Specification: California State Fire Marshall

Flame Test

UL Flame Test: NFPA 262

Plenum/Non-Plenum

Plenum (Y/N): Yes

Non-Plenum Number: 5220UL

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μH/ft)

.15

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

37.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.85

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

6.3 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6220UL D15U1000	1,000 FT	24.000 LB	BLUE		2 #16 FLRST FLRST
6220UL D15I1000	1,000 FT	24.000 LB	BLUE		2 #16 FLRST FLRST
6220UL 001U1000	1,000 FT	24.000 LB	BROWN		2 #16 FLRST FLRST
6220UL 002A1000	1,000 FT	26.000 LB	RED		2 #16 FLRST FLRST
6220UL 002U1000	1,000 FT	24.000 LB	RED		2 #16 FLRST FLRST
6220UL 002I1000	1,000 FT	24.000 LB	RED	C	2 #16 FLRST FLRST
6220UL 002500	500 FT	12.000 LB	RED		2 #16 FLRST FLRST
6220UL 003C500	500 FT	11.000 LB	ORANGE		2 #16 FLRST FLRST
6220UL 003U1000	1,000 FT	24.000 LB	ORANGE		2 #16 FLRST FLRST
6220UL 004C500	500 FT	11.000 LB	YELLOW		2 #16 FLRST FLRST
6220UL 004U1000	1,000 FT	24.000 LB	YELLOW		2 #16 FLRST FLRST
6220UL 004I1000	1,000 FT	24.000 LB	YELLOW		2 #16 FLRST FLRST
6220UL 007U1000	1,000 FT	24.000 LB	VIOLET		2 #16 FLRST FLRST
6220UL 009I1000	1,000 FT	24.000 LB	WHITE		2 #16 FLRST FLRST
6220UL 010I1000	1,000 FT	24.000 LB	BLACK		2 #16 FLRST FLRST

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 03-13-2013

© 2016 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the

6220UL Multi-Conductor - Commercial Applications - 2 Conductors Cabled

product.
Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).