

**3000K LED T3 and G4 Bi-Pin 2W 300 Degree**  
18207 (Black)

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_



**Certifications/Qualifications**

[www.kichler.com/warranty](http://www.kichler.com/warranty)

**Dimensions**

|        |       |
|--------|-------|
| Height | 1.25" |
| Length | 0.75" |
| Width  | 0.75" |

**Electrical**

|                         |             |
|-------------------------|-------------|
| Operating Voltage Range | 9-15VAC/VDC |
| Voltage                 | 12VAC/VDCV  |

**Photometrics**

|                                  |          |
|----------------------------------|----------|
| Beam Angle Options               | 300 Omni |
| Color Rendering Index            | 80       |
| Delivered Efficacy (Lumens/Watt) | 99       |
| Delivered Lumens                 | 200      |
| Kelvin Temperature               | 3000K    |

**Primary Lamping**

|                         |         |
|-------------------------|---------|
| Equivalent Light Source | Halogen |
| Expected Life Span      | 30000   |
| Volt-Amperes (VA)       | 3.18    |

**Product/Ordering Information**

|        |              |
|--------|--------------|
| SKU    | 18207.00     |
| Finish | Black        |
| UPC    | 783927532471 |

**Specifications**

|          |          |
|----------|----------|
| Material | ALUMINUM |
|----------|----------|

**Additional Finishes**



**Kichler**  
7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010  
Toll free: 866.558.5706 or kichler.com

**Notes:**  
1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.  
2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

**KICHLER®**