



Actual



Representative

Project: PROYECTO AMPLIACION TOQUEPALA
Location: PERU

CSE del PERU
LIMA

Catalog Number: LL67-G
Product ID: 7TAA087200R0023
UPC Number: 70450839317
EAN Number: 05415022310962
Status: Active

PVC Coated Conduit Body, LL Shape, Form 7, Size 2 Inch/53 Metric, Iron, Dark Gray

- A minimum of .040 inch PVC coating is bonded to the exterior.
- Covers are coated with a molded flange to seal the conduit body while the conduit body is molded with a flat surface on its opening to seal with the cover.
- Ocal pressure-sealing sleeves on all threaded hubs.
- Ocal conduit bodies are shipped with a cover and encapsulated stainless steel screws.
- Bodies are designed with a flat back, allowing more cubic inch capacity. The flat back also keeps the body more stable during installation, requiring fewer conduit straps.
- Provide openings for making splices and taps in conductors
- Connect conduit sections
- Provide taps for branch conduit runs
- Make 90° bends in conduit runs
- Provide for access to conductors for maintenance and future system changes

North American Specifications (UNSPSC)

| | |
|------------------|---|
| UNSPSC | 39131708 Electrical conduit fitting body |
| IGCC | 5563 Electrical conduit fitting body |
| Brand Name | Ocal |
| Type | Form 7 Conduit Body |
| Special Features | The Conduit Body and Cover are Double Coated with a Nominal .002 In. Blue Urethane on Both The Interior and Exterior, Before PVC Coating is Applied |
| Application | Act As Pull Outlets for Conductors Being Installed |
| Standard | UL E2969 |
| Hub Size | 2 Inch/53mm |
| Form | 7 |
| Length | 8.30 Inch |
| Width | 3.20 Inch |
| Height | 4.25 Inch |
| Material | Iron |
| Finish | PVC Coated |
| Color | Dark Gray |

Packaging

| | |
|---------------------------|------------------|
| Outer Quantity | 6 |
| Outer Dimensions (inches) | 16.25x13.75x7.25 |
| Weight Uom | 5.88 lbs. Each |

Documents / Support Tools

| | |
|---------------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
| Technical Drawing / Data Sheet Canada | Available on Website |
| Support/Tools | Available on Website |
| Catalog US | Available on Website |

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com