



Timer Controls: Analog/Mechanical Time Switches

T104M | 24-Hour Mechanical Time Switch - Mechanism Only



T104M

24-HOUR MECHANICAL TIME SWITCH - MECHANISM ONLY

The T100 Series Mechanical Time Switch has proven it can stand the test of time. These dependable time switches can handle electrical loads up to 40 A per pole and allow for up to 12 ON/OFF operations per day. A manual override switch provides added convenience.



Features & Applications

Features

- Direct 24-hour control of most loads

Applications

- Indoor/Outdoor Lighting

- Up to 12 ON/OFF operations each day with minimum ON/OFF times of one hour
- Manual override
- One ON and one OFF tripper included
- Signs
- Filters
- Electric Fences
- Fans
- Conveyors
- Pool Heaters
- Blowers
- Pumps
- Other Electrical loads


Specifications

Minimum ON/OFF Times 1 hour	Motor 2 HP, 24 FLA, 120 VAC, 60 Hz 5 HP, 28 FLA, 240 VAC, 60 Hz	Operating Temperature Min (°C) -40
Maximum ON/OFF Operations 12	Maximum Power Consumption (W) 3 W	Operating Temperature Min (F) -40
Has Override Switch No	Operating Temperature Max (°C) 54	Wire Size Max #8 AWG
Electronic Ballast 16 A, 277 VAC, 60 Hz	Operating Temperature Max (F) 130	Warranty 1-year

Related Accessories and Parts (4)



22T338GR



**MOUNTING BRACKET FOR INTERMATIC
STANDARDIZED TIMER MECHANISMS**


156T1978A



**1 SET OF ON/OFF TRIPPERS FOR T100,
T7000, AND WH40**

156T1978AD12

**12 PACK OF 156T1978A TRIPPERS FOR
T100, T7000, AND WH40**



WG1573-10D

**208-277 VAC, 60 HZ MOTOR FOR T102, T104,
T106, T172, T174, WH40**