



Now, more is less. Economical retrofit downlights with more to offer. Available in standard or adjustable heads.

Color: White

Weight: 0.5 lbs

**Project:**

**Type:**

**Prepared By:**

**Date:**

#### Driver Info

Type: Constant Current  
 120V: 0.093A  
 208V: 0.16A  
 240V: 0.14A  
 277V: 0.12A  
 Input Watts: 11W  
 Efficiency: N/A

#### LED Info

Watts: 11W  
 Color Temp: 3000K (Warm)  
 Color Accuracy: 90 CRI  
 L70 Lifespan: 50000  
 Lumens: 726  
 Efficacy: 69 LPW

## Technical Specifications

### Listings

#### UL Listing:

Suitable for damp locations

#### ENERGY STAR® V2.0:

This product is ENERGY STAR® Version 2.0 Certified.

#### IESNA LM-79 & IESNA LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

### Electrical

#### Driver:

Constant Current, Class 2, 50/60 Hz, 120V: 0.093A

#### Dimming:

TRIAC and ELV dimming compatibility.

#### THD:

27.43% at 120V

#### Power Factor:

95.6% at 120V

### LED Characteristics

#### LEDs:

Multi-chip, high-output, long-life LEDs

#### Lifespan:

50,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations

### Construction

#### Housing:

Precision, die-cast aluminum

#### Installation:

Jam clips for secure installation

#### Socket Adapter:

Edison 26 Medium Base Socket adapter

#### Lens:

Frosted acrylic lens

#### Finish:

Chip and fade-resistant polyester powder coat finish

#### Green Technology:

Mercury and UV-free. RoHS compliant components.

### Other

#### Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at

## Features

Superior thermal management with heat-dissipating fins

Specification-grade 90 CRI standard

Edison E26 Medium Base socket adapter included

5-Year, No-Compromise Warranty

## Ordering Matrix

Family	Size	Shape	Wattage	Color Temp
DLED	4	R	11	Y
	6 = 6" 4 = 4"	R = Round AR = Adjustable Round	14 = 14W 11 = 11W 9 = 9W	YN = 3500K (Warm Neutral) Y = 3000K (Warm) YY = 2700K (Residential Warm)