



Photocontrols : Fixed Mount Thermal Photocontrols

K4135 | Stem Mount Thermal Photocontrol, 480 V

K4135

STEM MOUNT THERMAL PHOTOCONTROL, 480 V

These photocontrols install on standard outdoor light fixtures and electrical boxes with 1/2" threaded or 7/8" punch-out holes for dusk-to-dawn ON/OFF control of outdoor lighting.



Features & Applications

Features

- Mechanical bimetal switch with Cadmium Sulfide photocell
- Delay feature prevents unwanted OFF switching
- Plastic and die-cast metal housing options
- 1/2"-14 NPSM threaded stem
- Washer gasket and locking nut included
- #18 AWG, 9" wire leads

Applications

- Exterior Lighting
- Street Lighting
- Parking Lot
- Pedestrian Pathway
- Landscape Lighting

Specifications

Photocontrol Style Stem Mount	Sensor Time Delay 30 sec to 90 sec	Cover Color Gray
Photocontrol Sensor Location Side	Wire Lead Length (in) 9	Product Height (mm) 76.2
Input Voltages Display 480 VAC, 50/60 Hz	Wire Lead Length (mm) 228.6	Product Width (mm) 39.7
Inductive 8.3 A, 480 VAC, 50/60 Hz	Operating Temperature Max (°C) 70	Product Depth (mm) 39.7
Incandescent Load Ratings 15 A, 480 VAC, 50/60 Hz	Operating Temperature Max (F) 158	Warranty 2-year limited
Activation Off 3 to 15 fc	Operating Temperature Min (°C) -40	
Activation On 1 to 5 fc	Operating Temperature Min (F) -40	

Related Accessories and Parts (2)



22LG116

**REPLACEMENT LIGHT GUARD FOR THERMAL PHOTOCONTROLS
(K4100 AND K4200 SERIES)**

K42-SW-A

SWIVEL ARM

Copyright © 2016 Intermatic Incorporated. All rights reserved.