



GE
Lighting

10310 - GE Daylight Starcoat® T8

F30T8/D

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	8 mg
Mercury-Picogram per mean lm hr	656.4
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1625 lm
Nominal Initial Lumen per Watt	62
Initial Lumens-nominal	1850 lm
Color Rendering Index-CRI	75
Color Temperature	6500 K

PRODUCT INFORMATION

Product Code	10310
Description	F30T8/D
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168103107
Standard Package GTIN	10043168103104
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168103107

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.1 in
Bulb Diameter (DIA) <Min>	0.94 in
Diameter	1.0 in
End of Base Pin to Pin	35.67 in
Face to End of Opposing Pin (B) <Max>	35.5 in
Face to End of Opposing Pin (B) <Min>	35.4 in
Nominal Length	36.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	30 W



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection installation or removal.



Jul 4, 2018 9:19:43 AM For additional information, visit www.gelighting.com