

SIMATIC ET 200SP, PROFINET bundle IM, IM 155-6PN ST, max. 32 I/O modules and 16 ET 200AL modules, single hot swap, bundle consists of: Interface module (6ES7155-6AU01-0BN0), Server module (6ES7193-6PA00-0AA0), BusAdapter BA 2xRJ45 (6ES7193-6AR00-0AA0)



General information

Product type designation	IM 155-6 PN ST
HW functional status	FS01
Firmware version	V4.1

Product function

- | | |
|---|--------------------------|
| <ul style="list-style-type: none"> • I&M data | Yes; I&M0 to I&M3 |
| <ul style="list-style-type: none"> • Module swapping during operation (hot swapping) | Yes; Single hot swapping |

Engineering with

- | | |
|---|---------------------|
| <ul style="list-style-type: none"> • STEP 7 TIA Portal configurable/integrated as of version | V14 |
| <ul style="list-style-type: none"> • STEP 7 configurable/integrated as of version | V5.5 SP4 and higher |
| <ul style="list-style-type: none"> • PROFINET as of GSD version/GSD revision | V2.3 / - |

Configuration control

via dataset	Yes
-------------	-----

Supply voltage

Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V

permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Short-circuit protection	Yes
Mains buffering	
• Mains/voltage failure stored energy time	10 ms
Input current	
Current consumption (rated value)	450 mA
Current consumption, max.	550 mA
Inrush current, max.	3.7 A
I^2t	0.09 A ² ·s
Power	
Infeed power to the backplane bus	4.5 W
Power loss	
Power loss, typ.	1.9 W
Address area	
Address space per module	
• Address space per module, max.	256 byte; per input / output
Address space per station	
• Address space per station, max.	512 byte; Dependent on configuration
Hardware configuration	
Rack	
• Modules per rack, max.	32; + 16 ET 200AL modules
Submodules	
• Number of submodules per station, max.	256
Interfaces	
Number of PROFINET interfaces	1; 2 ports (switch)
1. Interface	
Interface types	
• Number of ports	2
• integrated switch	Yes
• RJ 45 (Ethernet)	Yes; Pre-assembled BusAdapter BA 2x RJ45
• BusAdapter (PROFINET)	Yes; Applicable BusAdapter: BA 2x RJ45, BA 2x FC
Protocols	
• PROFINET IO Device	Yes
• Open IE communication	Yes
• Media redundancy	Yes; PROFINET MRP
Interface types	
RJ 45 (Ethernet)	
• Transmission procedure	PROFINET with 100 Mbit/s full duplex (100BASE-TX)

• 10 Mbps	Yes; for Ethernet services
• 100 Mbps	Yes; PROFINET with 100 Mbit/s full duplex (100BASE-TX)
• Autonegotiation	Yes
• Autocrossing	Yes

Protocols

PROFINET IO Device

Services

— Isochronous mode	No
— Open IE communication	Yes
— IRT	Yes; with send cycles of between 250 µs and 4 ms in increments of 125 µs
— PROFINergy	Yes
— Prioritized startup	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	2

Redundancy mode

— MRP	Yes
— MRPD	No
— PROFINET system redundancy (S2)	No

Open IE communication

• TCP/IP	Yes
• SNMP	Yes
• LLDP	Yes

Isochronous mode

Isochronous operation (application synchronized up to terminal)	No
---	----

Interrupts/diagnostics/status information

Status indicator	Yes
Alarms	Yes
Diagnostic functions	Yes

Diagnostics indication LED

• RUN LED	Yes; Green LED
• ERROR LED	Yes; Red LED
• MAINT LED	Yes; yellow LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Connection to network LINK (green)	Yes; 2x green link LEDs on BusAdapter

Potential separation

between backplane bus and electronics	No
between PROFINET and all other circuits	Yes; 1500 V AC
between supply and all other circuits	No

Permissible potential difference	
between different circuits	Safety extra low voltage SELV
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Network loading class	2
Security level	According to Security Level 1 Test Cases V1.1.1
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	0 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	0 °C
• vertical installation, max.	50 °C
Connection method	
ET-Connection	
• via BU/BA Send	Yes; + 16 ET 200AL modules
Dimensions	
Width	50 mm
Height	117 mm
Depth	74 mm
Weights	
Weight, approx.	190 g; IM 155-6 PN BA with 2x RJ45 ports and server module
last modified:	07/13/2018