

PHILIPS

Downlighting

Flat downlight

4" and 6" square aperture



Philips LED Flat downlight provides an easy and quick downlight solution without the traditional frame and reflector. Perfect for installation in existing ceilings or new construction with the benefits of energy saving LED technology.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Fixture

example: FDL6S09930TE1W

Family	Size	Lumens	CRI	CCT	Dimming	Voltage	Finish
FDL			9	30	TE	1	W
FDL Flat downlight	4S 4-inch Square	07 700 lm	9 90	30 3000K	TE Triac & ELV	1 120V	W White (matte)
	6S 6-inch Square	09 900 lm	9 90	30 3000K	TE Triac & ELV	1 120V	W White (matte)

Accessories

example: FDL5N

Family	Model
FDL	
FDL Flat Disk	SN Square new construction plate
	06C 6' extension cable
	20C 20' extension cable

Features

- Flange:** aluminum, painted white.
- Lens:** diffuser is used for smooth and diffused light pattern.
- Junction Box:** steel, 4 7/8" x 1 1/4" x 4 1/8" (124mm x 32.6mm x 105.2mm). Clip attached on the side of the J-box to connect with fixture or new construction plate to meet NEC (National Electric Code). J-box also has key holes on the side for mounting on joist (see page 2).
- Connector:** locking power connection is used to connect J-box and fixture. Standard length of the connection is 16" (400mm). Extension cable available as accessory.
- Ceiling cutout:** installation template on adhesive backed label is supplied with the product.
4" square: 4 3/16" x 4 3/16" (106 x 106mm) diameter.
6" square: 6x6" (152 x 152mm) diameter.
- Gasket:** foam gasket supplied with fixture.
- New Construction plate:** steel, 10" x 17 1/2" (254mm x 445mm). Holes on the side of the plate for mounting.

Electrical

Electronic power supply:

RoHS compliant.*
Class 2 power unit.

Remote power supply can only accommodate one LED module and cannot be shared with other LED module. Fixture can be through wired.

Dimming: Compatible for ELV/TRIAC (120V) dimmers.

Philips SR1000VA120 TRIAC (100%-1%)
 Leviton IPL06 TRIAC (100%-1%)
 Leviton 6615-PO ELV (100%-2.5%)
 Lutron CT-600P TRIAC (100%-1%)
 Lutron SCL-153P TRIAC (100%-1%)
 Lutron SELV-300P ELV (100%-1%)

	Lumen output	Input voltage	Input freq	Max. input current	Max. input power	Max. THD	Power factor
4" Square	700lm	120V	60Hz	0.13A	13W	15.3%	1
6" Square	900lm	120V	60Hz	0.15A	15.5W	14%	1

* Restrictions on Hazardous Substances (RoHS) is a European directive (2002/95/EC) designed to limit the content of 6 substances [lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB), and polybrominated diphenyl ethers (PBDE)] in electrical and electronic products. For products used in North America compliance to RoHS is voluntary and self-certified.

Labels

cULus listed (UL 1598) for wet locations (covered ceiling only). IC rated for direct contact with thermal insulation.

AirSeal for minimal air leakage.

ENERGY STAR® certified.

Title 24 compliant.

Warranty

Lifetime: Expected lifetime 50,000 hours and backed by a 5-year warranty (visit philips.com/warranties for details).

Lighttogo




Flat downlight square LED


4" and 6" aperture surface mount

Dimensions

Flat Downlight 4"



Flat Downlight 6"




Components


1. Electrical Box with knockouts
2. Mounting keyhole
3. Remodel NEC* clip
4. 19.5" (0.5m) cord
5. Locking power connector
6. Integrated LED Luminaire
7. Spring clip for easy mounting

* National Electric Code


Frame plate



Secure J-Box to frame plate:
slide junction box clip into slot and catch finger tab.




Junction box



Remodeler applications:

attach junction box clip to installation spring to assure N.E.C compliance.




Lighttogo

Flat downlight square LED

4" and 6" aperture surface mount

4-inch, 12W, 59.0 lm/W

Candela Curve



Fixture: **FDL4S07930KTE1W**

Output lumens: 684 lm
Input watts: 11.6 W
CRI: 90 min
CCT¹: 3000K
Spacing Crit.: 1.3
Beam Angle: 113°

Zonal summary

Zone	Lumens	%Luminaire
0-30	184	27.0%
0-40	302	44.1%
0-60	534	78.1%
0-90	684	100.0%

Angle	Mean CP	Lumens
0	238	
5	237	
10	234	
15	229	
20	221	
25	212	
30	201	
35	188	
40	174	
45	158	
50	142	
55	124	
60	105	
65	86	
70	67	
75	48	
80	29	
85	13	
90	0	

Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam diameter (ft)*
5'	10	6.5'
6'	7	7.8'
7'	5	9.1'
8'	4	10.4'
9'	3	11.7'

* Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq. ft.
5'	27.3	0.51
6'	17.9	0.34
7'	12.8	0.24
8'	10.7	0.20
9'	8.5	0.16

38' x 38' x 10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances


Efficacy: 59.0 lm/w
Report#: PR7060902

Coefficients of utilization

Ceiling	80%				70%		50%		30%		0%	
Wall	70	50	30	10	50	10	50	10	50	10	0	
RCR	Zonal cavity method - Effective floor reflectance = 20%											
Room Cavity Ratio	0	119	119	119	119	116	116	111	111	106	106	100
	1	109	104	99	95	101	94	97	91	93	88	83
	2	99	90	83	77	88	76	85	75	81	73	69
	3	90	79	71	64	77	64	74	62	72	61	58
	4	82	70	61	54	69	54	66	53	64	52	49
	5	75	62	53	47	61	46	59	46	57	45	43
	6	70	56	47	41	55	40	53	40	52	40	37
	7	65	51	42	36	50	36	49	35	47	35	33
	8	60	46	38	32	46	32	44	32	43	31	29
	9	56	43	34	29	42	29	41	29	40	28	26
10	53	39	31	26	39	26	38	26	37	26	24	

6-inch, 14W, 64.1 lm/W

Candela Curve



Fixture: **FDL6S07930KTE1W**

Output lumens: 891 lm
Input watts: 13.9 W
CRI: 90 min
CCT¹: 3000K
Spacing Crit.: 1.3
Beam Angle: 113°

Zonal summary

Zone	Lumens	%Luminaire
0-30	239	26.8%
0-40	391	43.9%
0-60	694	77.9%
0-90	891	100.0%

Angle	Mean CP	Lumens
0	308	
5	307	
10	303	
15	296	
20	287	
25	275	
30	261	
35	245	
40	226	
45	206	
50	185	
55	162	
60	138	
65	113	
70	88	
75	63	
80	39	
85	17	
90	0	

Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam diameter (ft)*
5'	12	6.5'
6'	9	7.8'
7'	6	9.1'
8'	5	10.4'
9'	4	11.7'

* Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq. ft.
5'	35.6	0.62
6'	23.4	0.40
7'	16.7	0.29
8'	13.9	0.24
9'	11.1	0.19

38' x 38' x 10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

Efficacy: 64.1 lm/w
Report#: PR7060904

Coefficients of utilization

Ceiling	80%				70%		50%		30%		0%	
Wall	70	50	30	10	50	10	50	10	50	10	0	
RCR	Zonal cavity method - Effective floor reflectance = 20%											
Room Cavity Ratio	0	119	119	119	119	116	116	111	111	106	106	100
	1	109	104	99	95	101	94	97	91	93	88	83
	2	99	90	83	77	88	76	85	75	81	73	69
	3	90	79	71	64	77	63	74	62	72	61	58
	4	82	70	61	54	69	54	66	53	64	52	49
	5	75	62	53	46	61	46	59	46	57	45	43
	6	70	56	47	41	55	40	53	40	52	40	37
	7	64	51	42	36	50	36	48	35	47	35	33
	8	60	46	38	32	46	32	44	32	43	31	29
	9	56	43	34	29	42	29	41	28	40	28	26
10	53	39	31	26	39	26	38	26	37	26	24	

1. Correlated Color Temperature within specs as defined in ANSI_NEMA_ANSI C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.
2. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.

© 2017 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.
philips.com/Lighttogo



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008