




GE  
Lighting



261  
kWh/1000h

E  
energy class

11  
lumens/watt

PAR 56

240PAR56/VNSP 12V

20575

## Product information

PAR lamps provide a robust and flexible design solution for a wide range of applications. Choice of PAR36, PAR46, PAR56 or PAR64

- 3000 K or 4200 K colour temperature
- Choice of beam widths
- Excellent colour rendering
- High efficiency combined with low operating costs
- Robust and reliable
- UV control
- Easy retrofit
- Colour consistent throughout life
- Colour blends with halogen and fluorescent

## Application areas



Club and Disco



WORLDWIDE PARTNER

## Product data

Product Code	20575
Bulb Shape	PAR
Bulb Finish	Aluminized
Bulb Diameter [mm]	177.8
Maximum Overall Length [mm]	127
Net weight per piece [g]	638
Gross weight per piece [g]	695
Brand	General Electric (GE)
Cap/Base	Screw terminal

## Performance data

Nominal beam angle [°]	15
Nominal center beam candlepower (CBCP) [cd]	140000
Weighted energy consumption [kWh/1000h]	260.08
Energy efficiency class (EEC)	E
Rated Life [h]	2000
Nominal lumens [lm]	2570

## Electrical data

Coil type	C-6
Ballast Required	Yes
Nominal power [W]	240
Nominal lamp voltage [V]	12

## Logistic data

DUN Code	00043168205757
Pack Quantity	12
Layer quantity	1 UK
Layer quantity UK	1
Pallet quantity UK (PC)	324
Outer case size	349 x 300 x 446 (mm)
Product status	Available

## Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Entertainment Solution Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[Entertainment Solution Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[High-res images / Technical drawings \(HTTP\)](#)

[Certificate for the Quality Management System of GE Lighting EMEA \(PDF\)](#)

[Certificate for the Environmental Management System of GE Lighting EMEA \(PDF\)](#)

## Disclaimer

Special purpose lamp – Stage Studio. Not suitable for household illumination.