

Product Number: 21879

Order Abbreviation: FBO31/841

General Description: 31W, 22.5" MOL, T8 OCTRON Curvalume fluorescent lamp, 1 5/8" leg spacing, 4100K color temperature rare earth phosphor, 82 CRI, suitable for IS or RS operation



Product Information

| | |
|------------------------------|----------------------|
| Abbrev. With Packaging Info. | FBO31841 15/CS 1/SKU |
| Average Rated Life (hr) | 20000 |
| Base | Medium Bipin |
| Bulb | T8 |
| Color Rendering Index (CRI) | 82 |
| Color Temperature/CCT (K) | 4100 |
| Family Brand Name | Octron® 800 |
| Initial Lumens at 25C | 2725 |
| Nominal Wattage (W) | 31.00 |



Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- The life rating of OCTRON and OCTRON Curvalume lamps operated on magnetic rapid start ballasts is 20,000 hours. The life rating of OCTRON and OCTRON Curvalume lamps operated on instant start electronic ballasts is 15,000 hours.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- OCTRON lamps should be operated only with magnetic rapid start ballasts designed to operate 265 mA, T-8 lamps or high frequency (electronic) ballasts that are either instant start, or rapid start, or programmed rapid start specifically designed to operate T8 lamps. OCTRON lamps may be operated on instant start or programmed rapid start ballasts with ballast factors ranging from a minimum of 0.71 to a maximum of 1.20 at the nominal ballast input voltage (see ballast specs for details). When OCTRON lamps are operated in the instant start mode, the two contacts (bi-pin lamps) of each rapid start lampholder/socket should be connected to each other or use "shunted" circle I lampholders/sockets for instant start bi-pin lamps. Always disconnect power before servicing installations and wire per the ballast schematics and National Electric Code.
- Approximate length of OCTRON CURVALUME lamps is measured from base face to outside of glass bend.
- For optimum performance OCTRON CURVALUME 1 5/8 inch leg spacing lamps in the 3000K, 3500K and 4100K color temperatures are now available only in the 82CRI version (800 series). These lamps are made to the same color standards and may be used in combination with other SYLVANIA OCTRON lamps to meet the needs of lighting installations where T8 lamps are used.