



GE
Lighting

25781 - GE soft white 40 watt R16 floodlight 1-pack

40R16/CD

- ☞ Use original GE's Soft White when you need a light without glare and harsh shadows.
- ☞ Replace ordinary light bulbs with GE Flood and Spotlight in all your track and recessed lighting fixtures.
- ☞ 2500K soft white light appearance
- ☞ Estimated yearly energy costs \$4.82 based on 3 hours per day \$0.11 per kWh
- ☞ GE soft white indoor spotlights provide warm, pleasing everyday light without harsh glares and shadows. These bulbs' funnel shape and reflective coating help direct light where it is needed better than a standard incandescent bulb
- ☞ Lasts 1.4 years based on 3 hours per day usage
- ☞ 280 lumens providing subtle, reassuring™ light
- ☞ R16 indoor floodlight with medium base for use in directional fixtures such as recessed can lighting

Product Photo



CAUTIONS & WARNINGS


Warning

Unexpected lamp rupture may cause injury, fire, or property damage

- Avoid direct water
- liquid or metal contact.

Risk of Fire

Keep combustible materials away from lamp.



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Filament	CC-6
Rated Life Hours-nominal	1500 h
Primary Application	Indoor Spotlight
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E26
Bulb Shape	R16

PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	225 lm
Color Temperature	2500 K

PRODUCT INFORMATION

Product Code	25781
Description	40R16/CD
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168257817
Standard Package GTIN	30043168257818
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168257817
Alternative Unit Of Measure	EACH
Standard Package Quantity	30
Ean UPC	043168257817
Standard Package GTIN	00043168257817
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
Sales Unit	Each
UCC	043168257817

DIMENSIONS

Diameter	2.0 in
----------	--------

ELECTRICAL CHARACTERISTICS

Wattage	40 W
Input Voltage [nom]	120 V

Jan 6, 2017 11:22:13 AM For additional information, visit www.gelighting.com