


# LED Aluminum Deck Light (DAL1) Specification Sheet

Project Name:	Location:	MFG: Philips Hadco
Fixture Type:	Catalog No.:	Qty:

## Ordering Guide

Example: DAL1 A LED2W

<b>Product Code</b>	DAL1	LED Aluminum Deck Light
<b>Finish</b>	A B G H	Black White Verde Bronze
<b>LED</b>	LED2W	LED Lamp



## Specifications

### HOUSING:

Body and mounting plate are cast aluminum construction. Fasteners are 300 series stainless steel.

### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

### OPTICAL ASSEMBLY:

Frosted, annealed glass lens Reflector is Stamped Hammertone Aluminum

### LAMPING:

Philips 12V LED 1.2W Capsule lamp. Up to 88% energy savins when compared to a 10W Capsule halogen lamp. Long lifetime of 15,000 hours (B50.L70). Operating temperature range is between -20C and 35C (ambient). Suitable for use in enclosed luminaires where the case temperature (Tc) remains below Tc MAX. Total Lumens = 105lm Lower wattage lamps are acceptable.

### ELECTRICAL ASSEMBLY:

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 12 volt fixture is pre-wired with 6-ft. pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

### INSTALLATION & MOUNTING:

Two (2) Stainless #8 wood screws (supplied) via key slots.

### WARRANTY:

Five-year limited warranty.

### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

### Height :

3 1/2" (89mm)

### Width:

3 1/2" (89mm)

### Depth:

1 7/8" (48mm)

### Max. Weight:

0.30 lb