



GE
Lighting

48868 - GE Ecolux® Blax® T4 - Facilities. Retail Display. Hospitality.

Office. Restaurant. Warehouse

F70QBX/841/A/ECO

☞ Super long life

Product Photo



GENERAL CHARACTERISTICS

Base Type	Pin/Plug-In
Mercury Content	3 mg
Rated Life Hours-nominal	12000 h
Starting Temp (MIN) C-degrees	-20 °C
Mercury-Picogram per mean lm hr	55.9
Primary Application	Facilities Retail Display Hospitality Office Restaurant Warehouse
Product Technology	Compact Fluorescent
Base	GX24q-6
Bulb Shape	T4

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	4470 lm
Nominal Initial Lumen per Watt	74
Initial Lumens-nominal	5200 lm
Color Rendering Index-CRI	82
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	48868
Description	F70QBX/841/A/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168488686
Standard Package GTIN	10043168488683
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168488686

DIMENSIONS

Nominal Length	8.19 in
Bulb Max Overall Length-MOL	8.19 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	250 W
Supply Current Freq nominal Hz	20 Hz
Rated power (Watts)	70 W

CAUTIONS & WARNINGS

Caution

Lamp may shatter and cause injury if broken

Remove and install by grasping only plastic portion of the lamp.

NOTES

4-Pin lamp minimum starting temperature is a function of the ballast. Most ballasts are rated with a minimum starting temperature of 50 degrees F (10 C). Ballasts are also available that provide reliable starting to 0 degrees F (-18C) and -20 F (-29C).