




Technology that saves lives

Multi-Voltage Control Relay

Model PAM1



Overview

The PAM1 Relay is encapsulated multi-voltage device providing 10 Amp Form C contacts. The relay may be energized by one of three input voltages: 24 Vac, 24 Vdc, or 115 Vac.

A red LED is provided which, when illuminated, indicates the relay coil is energized.


The PAM1 may be mounted by using the double-sided adhesive tape, the self-drilling screw, or loosely placed in a back box.

The PAM1 is ideal for applications where remote relays are required for control or status feedback. They are suitable for use with HVAC, Temperature Control, Fire Alarm, Security, Energy Management, and Lighting Control Systems.

Standard Features

- Completely encapsulated 10 Amp relay
- Relay may be energized by one of three input voltages
- Contains a red LED which illuminates when relay coil is energized
- May be mounted by double-sided adhesive tape, self-drilling screw or placed in back box
- Convenient 6 in (150mm) wire leads for electrical connections

Wiring





Technology that saves lives

Contact us...

Email: kidde.fire@fs.utc.com

Web: Kidde.com/EngineeredSystems

Kidde is a UTC brand.
1016 Corporate Park Drive
Mebane, NC 27302

© 2016 United Technologies Corporation.
All rights reserved.

Specifications

Power Requirments	15 mA per position @ 24 Vdc, 24 Vac, 115 Vac
Relay	UL Recognized SPDT
Contact Rating	10 Amps @ 115 Vac
Ambient Temperature	-58°F to 185°F (-50°C to 85°C)
Approvals	UL Recognized components
Dimensions	1.5 H x 1 W .875 D inches (38.1 x 24.5 x 22.2 mm) with 6 inch (150mm) wire leads 18 AWG (1.00mm ²)

Ordering Information

Model	Description
PAM1	Single SPDT relay with LED double-sided adhesive tape, mounting screw and 6 in (150 mm) leads.