



Powering Business Worldwide

pe.eaton.com

Type QCF 1/2-inch Quicklag Industrial Thermal-Magnetic Circuit Breaker

QCF2050

UPC:786679143421

Dimensions:

- **Height:** 1.2 IN
- **Length:** 5 IN
- **Width:** 3.2 IN

Weight:.55 LB

Notes:Standard Breaker terminals are box type lugs.

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag
- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Trip Type:** Non-Interchangeable
- **Mounting:** Front
- **Circuit Breaker Type:** QCF
- **Connection:** Cable-in/Cable-out

Supporting documents:

- [Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



