

Siemens Low Voltage Residential Specialty Load Centers: Murray Load Centers 3094.476 for residential applications. Meets stds: UL. Rated 120/240V (200A). Overload, short circuit protection by integrated circuit breaker. (AIR 22000AIC). Outdoor Type 3R enclosure with surface mounting. Special features: ul



| | |
|------------------------------|-------------|
| Configuration of the busbars | 200A |
| Mounting type | Surface |
| Phase number | 1 |
| Suitability for operation | Residential |

Electricity

| | |
|--|-------|
| Ampacity | 200 A |
| Voltage between phase and Ground (GND) rated value | 120 V |
| Voltage between phase and phase rated value | 240 V |

Switching capacity

| | |
|---|---------|
| Switching capacity current acc. to EN 60898 rated value | 22000 A |
|---|---------|

Model

| | |
|-------------------------|--------------|
| product brandname | Murray |
| Product sub brand name | Load Centers |
| Special product feature | UL |

Mechanical Design

| | |
|--|----|
| Number of width units for installation width | 40 |
|--|----|

| | |
|---------------------------------|-------------|
| Size of the circuit-breaker | MB |
| Width [in] | 3094.476 in |
| General product approval | |
| Certificate of suitability | UL |
| last modified: | 09/12/2017 |