



This economical linear LED washdown fixture is ideal for canopies, loading docks, tunnels, stairwells and other hard-to-reach areas where relamping is difficult and costly.

Color: White

Weight: 21.4 lbs

Project:

Type:

Prepared By:

Date:

Driver Info

Type: Constant Current
 120V: 0.89A
 208V: 0.52A
 240V: 0.45A
 277V: 0.38A
 Input Watts: 97W
 Efficiency: N/A

LED Info

Watts: 100W
 Color Temp: 4000K (Neutral)
 Color Accuracy: 84 CRI
 L70 Lifespan: 50,000
 Lumens: 11,436
 Efficacy: 118 LPW

Technical Specifications

Listings

UL Listing:

Suitable for wet locations

IESNA LM-79 & LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

DLC Listed:

This product is on the Design Lights Consortium (DLC) Qualified Products List and is eligible for rebates from DLC Member Utilities.
 DLC Product Code: PU3S9J3O

Electrical

Driver:

Constant Current, Class 2, 120-277V, 50/60Hz, 120V: 0.89A, 208V: 0.52A, 240V: 0.45A, 277V: 0.38A

Dimming Driver:

Driver includes dimming control wiring for 0-10V dimming systems. Requires separate 0-10V DC dimming circuit. Dims as low as 10%.

THD:

8.6% at 120V, 11.6% at 277V

Power Factor:

99.5% at 120V, 97.2% at 277V

LED Characteristics

LEDs:

Long-life, high-efficacy surface mount LEDs

Lifespan:

50,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations

Color Stability:

LED color temperature is warrantied to shift no more than 200K in CCT over a 5 year period

Color Uniformity:

RAB's range of CCT (Correlated Color Temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

Construction

IP Rating:

Ingress Protection rating of IP65 for dust and water (suitable for damp locations only when installed with Lightcloud Sensor)

Housing:

Impact-resistant polycarbonate with stainless steel door clips. 1/2" opening/ drill out (drill out by customer) for conduit and bushing/cord entry.

Mounting:

Quick-mount, stainless steel snap on brackets supplied for surface mounting. V-Hook brackets supplied standard for suspending the fixture.

Lens:

Diffuse polycarbonate lens for low glare and maximum protection

Gaskets:

High temperature silicone gaskets

Cold Weather Starting:

The minimum starting temperature is -20°C (-4°F)

Maximum Ambient Temperature:

Suitable for use in 40°C (104°F)

Installation:

6ft 5-wire cord installed on fixture for easy installation on SEAL8. Tether Cables are provided for easy installation. Quick connector may be used for quick and easy wiring.

Green Technology:

Mercury and UV-free. RoHS compliant components.

Finish:

Formulated for high-durability and long lasting color

Other

5 Yr Limited Warranty:

The RAB 5-year, limited warranty covers light output, driver performance and paint finish. RAB's warranty is subject to all terms and conditions found at


Equivalency :

Equivalent to 32W 4 Lamp T8 or 59W 2 Lamp T8

Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Dimensions



Features

- Includes V hooks for chain mounting and brackets for surface mounting
- 6 ft, 5-wire cord included for easy installation
- Stainless steel fastening clips
- IP65 Rated
- 0-10V dimming
- 50,000-Hour LED lifespan
- 5-Year, Limited Warranty

Ordering Matrix

Family	Length	Wattage	Color Temp	Driver	Options
SEAL	8	100	N	/D10	^
	4 = 4 ft	50 = 50W	Blank = 5000K (Cool)	/D10 = 0-10V Dimming 120-277V	Blank = No Option
	8 = 8 ft	100 = 100W	N = 4000K (Neutral)		/LC = Lightcloud® Controller
					/LCS = Lightcloud® Sensor 120-277V