



## XTRAFLEX Liquidtight Conduit Tubing & Fittings

### T&B Catalog Number:

**UPC Number:**

LT38P

**Status:**

78621045064

**Description:**

Active

3/8 in. non-metallic liquidtight Bullet.

#### Features

Outside surface has friction reducing ridges.

Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.

Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.

Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.

#### Application

T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.

Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

#### General

Trade Size (inches)

3/8

Material

Thermoplastic

#### Dimension Information

Dimension A (inches) 0.570

Dimension B (inches) 1.595

Dimension C (inches) 1.354

Dimension D-Minimum Throat (inches) 0.417

A (mm) 14.48

B (mm) 40.51

C (mm) 34.39

D (mm) 10.59

#### Specifications

3dmodel

Available on Website

#### Packaging

T&B Inner Pack 20

Package in Units 100

T&B Sold in UOM Each

T&B Weight Per UOM 8.6 lbs. per 100

#### Application Support

T&B Instruction Sheets ta00998-tb2

Guide to Nonmetallic Conduit Applications Available on Website

XTRAFLEX System Specifications Available on Website

#### Certifications

RoHS Compliance

Yes

## Certifications



File Nbr:  
E 23018

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)