# CONSTRUCTION TRIPOLYMER SEALANT

## 1. PRODUCT NAME:

2300<sup>®</sup> Construction Tripolymer Sealant

#### 2. MANUFACTURER:

**Geocel Products Group** A Business Unit of The Sherwin-Williams Company

("Geocel Products Group") Cleveland, OH 44115 Phone: (800) 348-7615 Fax: (800) 348-7009 www.GeócelUSA.com

## 3. PRODUCT DESCRIPTION:

2300® Construction Tripolymer Sealant is a single component, high-performance elastomeric sealant for use in a wide variety of roofing, trim, architectural metal, manufacturing, underdeck system, solar roof system, and general construction applications.

#### **Product Benefits:**

- Will not crack
- Asphalt shingle compatible
- Exceptional elongation and flexibility
- Excellent adhesion to many building surfaces, even when damp
- UV resistant
- Resealable, may be applied over itself
- Paintable
- Easily applied, non-stringing formulation
- Available in crystal clear, colors, and specially designed metal roof colors
- Tools and cleans up easily
- Cured sealant is mildew resistant

#### **Basic Uses:**

- Most non-traffic-bearing joints, including those where structural movement or stress is expected
- · Primerless application to brick, concrete, metal, glass, treated and untreated wood, asphaltic materials, and vinyl
- · Where ultraviolet resistant material is required
- Where a paintable sealant is required
- As a trim sealant for metal components

Geoce Geore CONSTRUCTION Geoce CRYSTAL CLEAR

> Adheres To: Asphalt shingles. Modified Bitumen, coated steel (Kynar 500® based finishes), concrete, vinyl, steel, and other common building substrates.

#### **Composition and Materials:**

2300 Sealant is based on a proprietary formulation of polymers designed to provide optimum flexibility, adhesion, weather resistance, and durability. 2300 Sealant retains its flexibility due to the absence of plasticizers, which

tend to migrate out causing hardening and reduced durability. Due to the mild solvent blend contained in the sealant, 2300 Sealant is not a flammable liquid according to NFPA liquid guidelines. It is weather and ultraviolet light resistant. Its clear formulation is literally clear as glass from the moment of application.

Grade: Gun grade consistency

Primer: Not required on most surfaces. If primerless adhesion to a particular substrate is in question, a test application is recommended. Contact Geocel Products Group's Technical Service Department for further information.

## Packaging:

10.3 oz. Clear Plastic Cartridge

· Crystal Clear

10.3 oz. Plastic Cartridge

Standard Colors

10.3 oz. Composite Cartridge

Standard and Metal Roof Colors

29 oz. Composite Cartridge

 Clear, White, Gray, Black, Brown, Bronze, Tan, and Cedar

## Colors:

- · Standard: White, Gray, Black, Brown, Bronze, Tan, Cedar, Almond, Driftwood and Terra.
- · Many popular metal roof colors.
- · Addtional colors may be available upon request.

For other sizes and/or colors, please contact our Customer Support Center at 800-348-7615.

## **Limitations:**

- Do not use on traffic-bearing surfaces
- Do not use on extruded polystyrene insulating sheathing (foam board, etc.)
- · Do not use on acrylic skylight glazing surfaces
- Do not use in areas where food is processed or stored
- For exterior use only due to odor emitted during cure.
- · Do not use for potable water applications

## 4. INSTALLATION:

Joint Design: For optimum results, joints should be a minimum of 4 times greater than anticipated movement. Minimum recommended joint size is 1/4" x 1/4". Maximum joint size should be 1/2" x 3/8" in depth.

Kynar 500® is a registered trademark of Arkema Inc., and is used under license.

**Surface Preparation: Priming is not** required unless specified above. For best results joints should be basically clean and surface dry, although dampness from dew will not interfere with adhesion. Do not use xylene or MEK to clean joints or to remove surface coatings unless surface can be allowed to dry before application of sealant. If the joint is wet with solvent, the sealant will not adhere properly. Use of a dry rag or brush to remove dust, dirt, or other contaminants is recommended. Contamination from curing agents and form releases should be avoided. Contact Geocel Products Group's Technical Service Department or representative if such agents are involved.

Joint Backing: Joint depth should not exceed 3/8". An open cell backer rod should be used to control joint depth. In shallow joints, a bond breaker tape should be installed to prevent three-point contact.

Elongation: 1062% - Clear,

1180% - Colors

Tack Free: 45 minutes

Cure: 4 days

Application and Tooling: Apply with conventional caulking equipment, filling joint completely. When temperature is below 40° F, application will be easier if sealant is warmed. When temperature of surface to be sealed exceeds 140° F, do not apply sealant until surface cools. A soap solution or a solvent such as xylene may be used as a lubricant for tooling. Follow manufacturer's instructions for safe use. Do not allow tooling agents to contaminate open joints.

Painting: Sealant may be painted after 24 hours. If using a relatively inflexible paint, allow sealant to cure for 4 days before painting. 2300 Sealant may be coated with any latex and most oil-based paints. Some paints may crack in dynamic joints. See paint manufacturer's specifications.

Cleaning: Remove 2300 Sealant from gun and tools before it cures. This may be done by scraping and use of solvents such as MEK (lacquer thinner), xylene, Toluol or chlorinated solvents. Observe

manufacturer's precautions when using toxic or flammable solvents. Cured materials may be removed by cutting with sharp tools.

Storage Life: One year

**Cautions:** CONTAINS AROMATIC HYDROCARBONS. Contents are COMBUSTIBLE. Keep away from heat and open flame. VAPOR HARMFUL. Use only with adequate ventilation. To avoid overexposure, open windows and doors or use other means to ensure fresh air entry during application and drying. If you experience eye watering, headaches, or dizziness, increase fresh air, or wear respiratory protection (NIOSH approved) or leave the area. Avoid contact with eyes and skin. Wash hands after using. Keep container closed when not in use. Do not transfer contents to other containers for storage.

First Aid: In case of eye contact, flush thoroughly with large amounts of water for 15 minutes and get medical attention. For skin contact, wash thoroughly with soap and water. In case of respiratory difficulty, provide fresh air and call physician. If swallowed, call Poison Control Center, hospital emergency room, or physician immediately. DELAYED EFFECTS FROM LONG TERM OVEREXPOSURE. Contains solvents which can cause permanent brain and nervous system damage. Intentional misuse by deliberately concentrating and inhaling the contents can be harmful or fatal.

Warning: This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm. DO NOT TAKE INTERNALLY. KEEP OUT OF THE REACH OF CHILDREN.

### 5. AVAILABILITY AND COST:

2300 colors may not be sold in California. 2300 Crystal Clear may be sold in non-SCAQMD California counties only. Available from various construction material and industrial distributors. Cost and further technical data are available from your local Geocel Products Group representative or from our office.

### **6. LIMITED WARRANTY:**

If when applied according to label directions this product fails to perform in accordance with its published literature, upon satisfactory evidence of product failure, and as your sole remedy, we will either replace the product at no cost or refund the original purchase price for that portion of product that fails to perform in accordance with this limited warranty. Labor or costs associated with labor are not included. THIS LIMITED WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING MERCHANTABILITY, WHICH ARE ALL DISCLAIMED AND/OR LIMITED IN DURATION TO THE EXTENT PERMITTED BY LAW. WE SHALL NOT BE LIABLE FOR INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES (INCLUDING LOST PROFITS) FROM ANY CAUSE WHATSOEVER AND SUCH DAMAGES ARE EXPRESSLY EXCLUDED. Some states do not allow the exclusion or limitation of incidental or consequential damages or how long an implied warranty lasts, so the above limitation or exclusion may not apply to you. This limited warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

#### 7. MAINTENANCE:

No maintenance should be required. If the sealant is damaged, either remove bead and reseal with 2300 Sealant or apply additional 2300 Sealant over the damaged area.

# 8. TECHNICAL SERVICES:

Geocel Products Group representatives throughout the U.S. are available to provide technical assistance. Geocel Products Group's in-house technical staff and laboratory facilities are equipped to respond to specific requests for further information and/or applications testing.

COMPAR There is A Difference	E!	RYSTA	CLEA	ALE MILDEN	RESIE WET ST	TANT SU	cured RFACE USE BEI	OW 32°	OVERY ASY CI	EAN-U	RROSI	E OW S TO W	OOD TO BE	ACK W	SPHAL SPHAL SPHAL SPHAL SPHAL	AFAL MATT O COMPORERE LUMP 15 TO UNIT TO COMPORERE LUMP 15 TO UNIT TO COMPORERE LUMP 15 TO COMPORERE LUMP	ine
2300 <sup>®</sup>	•	•	•	•	•	•	•	•	•	•	•		•	•	•		
SILICONE						•				•		•	•				

THEORETICAL YIELD per 10.3 fl. oz cartridge

per 10.3 II. oz cartriage					
Joint Size	Linear Feet				
1/4" x 1/4"	24.8				
1/4" x 3/8"	16.5				
1/4" x 1/2"	12.4				
1/2" x 3/8"	8.7				

For additional product information, refer to the product spec sheet located at www.GeocelUSA.com.