

72" Vast Fan

 Ceiling mounted • Damp location listed **PROGRESS LED**

Description:

Beautiful and expansive in design, the 72 inch Vast ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a Brushed Nickel finish with Chrome accents and brushed nickel blades. Featuring an energy efficient DC motor with 18W light source, Vast is dimmable and offers a 3000K-color temperature. Damp location listed for covered outdoor areas, a full function remote control with batteries is included.

Specifications:

- Brushed Nickel (-09) (plated)
- Steel Construction
- Frosted Glass bowl
- Eight-blade 72" Vast ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefits.
- Vast ceiling fan features Brushed Nickel blades with a Brushed Nickel finish and Chrome accents.
- Beautiful and expansive in design, the 72" Vast ceiling fan is ideal for use in large areas, such as great rooms, family rooms for maximum cooling.
- The light kit contains a frosted glass shade and is comprised of a 18W dimmable 3000K LED module, offering 1400 lumens (source), 90+ CRI.
- Six speed full function remote control with batteries is included - and controls full range dimming and fan speed capabilities.
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet.
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately.
- Mounting hardware is included.
- Can be used to comply with California Title 20.
- High Speed Energy Information: Airflow- 7982 cfm, Energy consumption- 28 watts (excluding lights), Airflow efficiency- 285 cfm/watt.
- Limited Lifetime Warranty.
- Dimmable to 10% brightness
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting bracket for outlet box included
- 80' of wire supplied
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	18w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1400/77.8 (LM-82)
CCT	3000 K
CRI	90+
Life (hours)	(L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-10 °C
Max. Operating Temp	30 °C
Warranty	Limited Lifetime warranty
Labels	UL Damp location listed
	Meets California Title 24 JA8-2016

P2550-0930K

Images:



Dimensions:

 Diameter: 72"
 Height: 16-3/4"

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$15

\$3
|
\$34

Cost Range of Similar Models (19" – 84")

• Based on 12 cents per kWh and 6.4 hours use per day
 • Your cost depends on rates and use
 • Energy Use: 29 Watts

All estimates based on typical use, excluding lights

Airflow

7982

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
 • Airflow Efficiency: 273 Cubic Feet Per Minute Per Watt

ftc.gov/energy