



Representative Image

Catalog No. TH4364

Description: 200A 3P HD N1 600V FUSIBLE SW

UPC No 783164604825

Home > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Amperage	200 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	2-250
480 Vac, NEC Std, 1-ph	25 hp
480 Vac, NEC Std, 3-ph	50 hp
480 Vac, Time Delay, 1-ph	50 hp
480 Vac, Time Delay, 3-ph	125 hp
600 Vac, NEC Std, 1-ph	30 hp
600 Vac, NEC Std, 3-ph	60 hp
600 Vac, Time Delay, 1-ph	50 hp
600 Vac, Time Delay, 3-ph	150 hp
250 Vdc	40 hp

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	31,5 in
Depth	5,1 in
Width	13,3 in

Dimensions

Weight

33 lb

Publications

Title	Publication No.	Publication Type
Let's be clear		
Enhancements to Safety Switches: Clear line shield; bright red switches and factory installed neutrals	SSPostcard	Ads
200A - Safety Switches		
1 page outline drawing in .pdf format.	10103091SH105	Drawings-Outline and Dimensional

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.