

| roject: | | |
|--------------|--|--|
| ixture Type: | | |
| ocation: | | |
| Contact: | | |

FRESNO

Ceiling mounted • Dry location listed



Description:

Five-blade 60" Fresno ceiling fan features an LED light source, offering both form and function with energy- and cost-savings benefits. A white opal glass shade features an 18W dimmable, 3000K LED module. Full range dimming and remote control with batteries is included. Featuring reversible blades, the fan has a White finish. Can be used to comply with California Title 20. Can be used to comply with 2016 Title 24 JA8.

Specifications:

- · White (-30) (painted)
- · Steel construction
- · White opal glass bowl
- · Indoor ceiling fan ideal for use in great rooms, living rooms, bedrooms and bonus rooms
- The light kit contains a white opal glass shade and is comprised of a 18W dimmable 3000K LED module, offering 1400 lumens, 90+ CRI
- $\bullet \quad \text{A full function remote with batteries is included} \cdot \text{and controls full range dimming and fan speed capabilities including reverse} \\$
- $\bullet \quad \text{Oversized ceiling fan ideal for use in spacious areas, such as large great rooms, living rooms, bedrooms and bonus rooms}\\$
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- · Mounting hardware is included
- · Can be used to comply with California Title 20.
- · Dimmable to 10% brightness (See Dimming Notes)
- · Canopy covers a standard 4" octagonal recessed outlet box
- 80" of wire supplied
- · White blades, plywood construction
- 14 degree blade pitch
- · Full Function Remote Included
- · Triple capacitor speed control
- Meets California Title 24 JA8-2016
- · Airflow: 5718 CFM*
- · Energy consumtion: 79 watts (excluding lights)*
- Airflow efficiency: 72 cfm/watt*
- * Fan on a downrod

P2548-3030K

Images:




Dimensions:

Diameter: 60" Height: 17-1/4"

Performance:

| Number of Modules | 1 | |
|---------------------|------------------------------------|--|
| Input Power | 18w | |
| Input Voltage | 120 V | |
| Input Frequency | 60 Hz | |
| Lumens/LPW | 1400/77.8 (LM-79) | |
| ССТ | 3000 K | |
| CRI | 90+ | |
| Life (hours) | (L70/TM-21) | |
| EMI/RFI | FCC Title 47, Part 15 Class B | |
| Min. Start Temp | -30 °C | |
| Max. Operating Temp | 30 ℃ | |
| Warranty | Limited Lifetime warranty | |
| Labels | UL Dry location listed | |
| | Meets California Title 24 JA8-2016 | |





FRESNO

Ceiling mounted • Dry location listed PROGRESS LED

P2548-3030K

Dimming Notes:

P2548 is designed to be compatible with many controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

"Lutron - NTEVL-300

Lutron - DVELV-300P

Lutron - Caseta Wireless

Leviton - 6672

Leviton - 6674

Lutron - AYCL-153P

Lutron - AYLV-600P Lutron - MAELV-601

Leviton - AWRMG-EAW"

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.