



GE
Lighting

10147 - GE Warm White Starcoat® T8

F15T8/WW

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	18 mg
Mercury-Picogram per mean lm hr	3221.5
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	745 lm
Nominal Initial Lumen per Watt	56
Initial Lumens-nominal	845 lm
Color Rendering Index-CRI	52
Color Temperature	3000 K

PRODUCT INFORMATION

Product Code	10147
Description	F15T8/WW
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168101479
Standard Package GTIN	10043168101476
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168101479

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.1 in
Bulb Diameter (DIA) <Min>	0.94 in
Diameter	1.0 in
End of Base Pin to Pin	17.67 in
Face to End of Opposing Pin (B) <Max>	17.5 in
Face to End of Opposing Pin (B) <Min>	17.39 in
Nominal Length	18.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Open Circuit Voltage (rapid start) Min @ Temperature	157.00 V @ 10 °C
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	15 W

CAUTIONS & WARNINGS

Warning

Risk of Electric Shock

Turn power off before inspection
installation or removal.

Caution

Lamp may shatter and cause injury if broken
Wear safety glasses and gloves when handling lamp.
Do not use excessive force when installing lamp.



Jan 11, 2018 6:58:16 AM For additional information, visit www.gelighting.com