



GE
Lighting

10282 - GE garage & basement 25 watt T12 1-pack

F25T12CW/28 6PK

- ☞ Lasts 3.4 years based on 6 hours per day usage
- ☞ 1.5 inch diameter T12 with medium bi-pin (g13) base
- ☞ 4100K cool white light appearance
- ☞ Cool white light perfect for sizable spaces
- ☞ For use in large spaces such as basements and garages
- ☞ GE garage & basement fluorescent bulbs' cool white light is perfect for illuminating sizable spaces throughout your home. Use in large open spaces in your home including finished and unfinished basements, garages and rec rooms
- ☞ 28 inches long

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	60 mg
Mercury-Picogram per mean lm hr	5755.4
Rated Life Instant Start-Hrs	7500 h @ 3 h
Starting Temp (MIN) C-degrees	10 °C
Bulb Material	Soda lime
Rated Life Hours-nominal	7500 h
Primary Application	Appliance

Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T12

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1390 lm
Nominal Initial Lumen per Watt	62
Initial Lumens-nominal	1550 lm
Color Rendering Index-CRI	60
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	10282
Description	F25T12CW/28 6PK
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168981248
Standard Package GTIN	00043168102827
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168102827

DIMENSIONS

Bulb Diameter (DIA) <Max>	1.59 in
Bulb Diameter (DIA) <Min>	1.41 in
Diameter	1.5 in
End of Base Pin to Pin	27.67 in
Face to End of Opposing Pin (B) <Max>	27.5 in
Face to End of Opposing Pin (B) <Min>	27.4 in
Nominal Length	28.0 in

ELECTRICAL CHARACTERISTICS

Current Crest Factor (MAX)	1.7
Cathode Resistance Ratio - Rh/Rc (MIN)	4.250
Cathode Resistance Ratio - Rh/Rc (MAX)	6.500
Rated power (Watts)	25 W

CAUTIONS & WARNINGS

Warning

Risk of Electric Shock

Turn power off before inspection
installation or removal.

Caution

Lamp may shatter and cause injury if broken

Wear safety glasses and gloves when handling lamp.

Do not use excessive force when installing lamp.



Jan 6, 2017 10:54:08 AM For additional information, visit www.gelighting.com