




Power Limited-Type FPLR-Non Plenum Rated, Shielded-300 Volt



Product Construction

Conductor:

- Solid bare copper

Insulation:

- Color coded Polyvinyl Chloride

Assembly:

- Conductors cabled together

Shield:

- Overall Aluminum/polyester shield and drain wire

Jacket

- Red PVC

Applications

- Fire alarm systems
- Smoke detectors
- Burglar alarms
- Dedicated Fire Protective Circuits

Standards

- UL Listed Type FPLR
- NEC Article 760

Part #	AWG	Conductors	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
H31802	18	2	.006"	.015"	.144"	20
H31804	18	4	.006"	.015"	.166"	30
H31806	18	6	.006"	.015"	.190"	38
H31808	18	8	.006"	.015"	.215"	49
H31602	16	2	.007"	.016"	.180"	26
H31604	16	4	.007"	.016"	.199"	45
H31402	14	2	.010"	.021"	.222"	47
H31404	14	4	.011"	.021"	.233"	77
H31202	12	2	.010"	.021"	.245"	71

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.