

PHILIPS
Day-Brite
CFI

Recessed

FluxGrid 2x4

3800, 4200, 4300, 4800,
5400, or 7400 lumens



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lumens: _____ Qty: _____
Notes: _____

The Philips Day-Brite / Philips CFI FluxGrid LED recessed offers architectural appeal with “must have” features. Two different lens styles, discrete air handling, integral emergency, and access to the boards and driver from below make FluxGrid an ideal solution for a wide range of applications.

Ordering guide – Standard configurations available with all choices, unless otherwise noted.

Base configurations selections indicated by blue.

Example: 2FGG42B840-4-D-UNV-DIM

Width	Family	Ceiling Type	Air Function	Lumens	Color	Length	Center Diffuser	Voltage	Driver	Options
2	FG	G				4				
2 2'	FG FluxGrid	G Grid	Blank Static H Air return	<i>Standard Configurations</i> 38L 3800 nominal delivered lumens 43L 4300 nominal delivered lumens 48L 4800 nominal delivered lumens 54L 5400 nominal delivered lumens 74L 7400 nominal delivered lumens <i>Base Configurations</i> 42B 4200 nominal delivered lumens	830 80 CRI, 3000K 835 80 CRI, 3500K 840 80 CRI, 4000K 850 80 CRI, 5000K	4 4'	D Diffuse (ribbed) DS Diffuse (smooth)	UNV Universal voltage 120-277V 120¹ 120V 277¹ 277V 347 347V	DIM^{2,3} Dimming SDIM⁴ Step dimming to 40% input power XDIM¹ MarkX phase dimming L3D⁵ Lutron Hi-lume A 1% dimming LDE Lutron LDE5 5% dimming DALI DALI	F1 3/8" flex, 3 wire 18 gauge 6' F2 3/8" flex, 4 wire 18 gauge 6' F1/D 3/8" twin flex, 3 wire 18 gauge 6' for dimmable luminaires F2/5W 3/8" single flex, 5 wire 18 gauge 6' for dimmable luminaires F2/6W 3/8" single flex, 6 wire 18 gauge 6' for dimmable and EMLED luminaires GLR Fusing, fast blow EMLED⁶ Bodine BSL310 10W battery pack IAP⁷ Integral Interact Pro RF sensor, enables network lighting control SWZDT⁷ Integral sensor, daylighting and occupancy, advanced grouping with dwell time DAYOCC⁷ Integral sensor, daylighting and occupancy, basic grouping CHIC Chicago Plenum rated

Footnotes

- XDIM requires 120V or 277V specification. Not available on 30L package.
- Integral IAP, SWZDT and DAYOCC options dimmable to 5% via wireless wall switch. See p. 2.
- Non-controls configurations are 0-10V dimmable to 1% for standard configurations. Base configurations are 0-10V dimmable to 10%.
- Consult factory for SDIM on 74L package.
- Specify up to 43L package. Consult factory for higher lumen packages.
- Philips Bodine BSL310, 1100lm nominal delivered
- Specify DIM driver option only.

Accessories (order separately)

- **FMA24** – 2'x4' "F" mounting frame for NEMA "F" mounting
- **FGD4L** – FG 4' ribbed replacement lens
- **FGDS4L** – FG 4' smooth replacement lens
- **FGHD4L** – FG 4' air return ribbed replacement lens
- **FGHDS4L** – FG 4' air return smooth replacement lens
- **FSK24** – 2'x4' surface mount field installation kit (factory welded seams)
- **FSF24** – 2'x4' surface mount field assembly kit (field assembled)

Energy data

Luminaire	Catalog Number	Input Power	Efficacy
2x4 Standard	2FGG38L840	31.8	120
	2FGG43L840	36.2	119
	2FGG48L840	41.5	116
	2FGG54L840	48.9	114
2FGG74L840	69.2	106	
2x4 Base	2FGG42B840	33.9	124



interact
ready.

2FG FluxGrid LED recessed 2x4

3800, 4200, 4300, 4800, 5400, or 7400 lumens

Application

- 3" deep low profile configuration provides minimal penetration into the plenum space.
- Acrylic diffuser available in ribbed and smooth configurations provides even illumination with comfortable appeal.
- Standard and base configurations available in multiple lumen packages to suit the needs of various applications.
- Lambertian distribution creates uniform horizontal and vertical illuminance on the work plane and reduces scalloping on the walls.
- CRI 80 minimum color rendering with balanced spectrum.
- LEDs coupled with standard dimming provide prolonged lumen maintenance. Optional integral sensors contribute further to LED lumen maintenance.
- Designed for use with standard 15/16" wide Grid (NEMA "G") T-bars. Drywall or plaster applications require use with the FMA24 "F" mounting frame accessory (sold and shipped separately).
- Continuous row mounting is possible with a 1" gap between fixtures accommodated by others.

Enclosure

- Opal acrylic diffuser provides visually comfortable lumenance without compromise to luminaire efficacy.
- Diffuser requires no frames or fasteners and can be easily removed from below without the use of tools.

Construction/Finish

- Uncomplicated design is 3" deep with minimal material overlap creating several benefits:
 - Less material required
 - Less packaging required
 - Reduced weight for ease of handling and transit
 - Less energy required for construction and assembly
 - More luminaires can be shipped per truck to reduce fuel consumption
- Metal side covers are die formed with a conical shape to enhance light distribution and visual aesthetic.
- Injection molded lens retainers allow for easy, tool-free access to the LED boards and driver from below, and provide positive lens retention.
- Luminaire finish is matte white polyester powder coat for high quality, durable finish.
- T-bar grid clips are integral to the body.

- Air return option provides air flow through a unique lens retainer design. Air passes through architectural forms in the lens retainers (each end), and through the end plate of the luminaire. A cover plate is provided to control air flow through the luminaire, or make it static as required.
- Integral controls options include sensor mounted in one lens retainer. Controls are commissioned via intuitive Philips app on a Droid smartphone either through NFC or an IR blaster.
- EMLED option requires the emergency battery pack be installed with a top side cover. Access from above.
- To estimate lumen output in emergency mode, multiply emergency pack wattage by efficacy, then by 1.10.

General notes

- All options are factory installed.
- All accessories are field installed.
- Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

Electrical

- Integral sensor options for occupancy sensing and/or daylight harvesting are available for additional energy savings with no reduction of life or increase in installation labor.
- Standard configurations provide up to 120 lumens per watt and are available with 5 lumen packages and 3000, 3500, 4000, and 5000K color temperatures.
- Base configurations provide up to 124 lumens per watt and are available in 4200 lumen flux and 3500K and 4000K color temperatures.
- LED boards are accessible from below by removal of the lens. Lens removal is tool-free by compressing the sides and pushing to one end.
- LED driver is accessible from below by removal of the lens and integral wireway cover. The wireway cover is easily removed with a flat head screwdriver.
- Other driver options including step dimming (SDIM, 100%/40%), DALI, phase dimming (XDIM), and Lutron are available.
- Five year limited luminaire warranty includes LED boards and driver. Visit www.philips.com/warranties for complete warranty information.

- TM-21 predicted L70 lumen maintenance up to 70,000 hours.
- cETLus listed to UL and CSA standards, suitable for damp locations.
- FluxGrid luminaires are DesignLights Consortium qualified. Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>).

DAYOCC & SpaceWise DT (SWZDT)

- Commissioning via compatible Android phone and Philips Field App
- Dimming via compatible wireless wall switch only (see below)
- Register for the commissioning app at <http://registration.componentcloud.philips.com/appregistration/>
- Integral sensing options (DAYOCC, SWZG2, SWZDT) may not be combined
- For more information including recommended switches, refer to the following –
 - DAYOCC** – www.lightingproducts.philips.com/documents/webdb2/DayBrite/pdf/DAYOCC_sensor.pdf
 - SWZDT** – www.lightingproducts.philips.com/documents/webdb2/DayBrite/pdf/SWZDT_sensor.pdf



Interact Pro (IAP)

- Interact Pro brings the power of connected lighting to small and medium businesses without the complexity usually associated with connected lighting.
- Interact Pro includes an app, a portal and a broad portfolio of wireless Luminaires, lamps and retrofit kits all working on the same system.
- Commissioning via Interact Pro App (Android or iPhone)
- Prepare commissioning remotely via Interact Pro portal
- Requires compatible Interact Pro Gateway and internet connectivity for commissioning
- Compatible with UID8451/10 ZigBee Greenpower wireless dimmer switch
- Compatible with wireless Occ sensor (OCC SENSOR IA CM IP42 WH 10/1) or wireless Day/Occ sensor (OCC MULTI SENSOR IA CM WH 10/1)
- For more information on Interact Pro visit: www.interact-lighting.com/pro
- For more information on Interact Ready visit: www.philips.com/interactready

2FG FluxGrid LED recessed 2x4

3800, 4200, 4300, 4800, 5400, or 7400 lumens


Dimensions



Controls sensor integrated into one lens retainer.




The air return option allows air to flow through vents in the lens retainers on each end. Air blades are provided on each end of the luminaire to control air flow to the plenum.



2FG FluxGrid LED recessed 2x4

3800, 4200, 4300, 4800, 5400, or 7400 lumens

Air return



Return air - noise criteria

All luminaire sizes

		CFM							
Mode		27	37	53	62	71	80	90	102
Air ¹	NC (dB)	<15	24	25	29	33	35	38	40

		CFM							
Mode			31	38	45	51	61	65	74
Air+Controls ²	NC (dB)		<15	19	21	25	28	30	34

1. Air-only option includes air return lens retainers and pattern control blades on both ends of luminaire.
2. Air+Controls includes the air return lens retainer and pattern control blade on one end of the luminaire. Control lens retainer on the other with matching width.

2FG FluxGrid LED recessed 2x4

3800, 4200, 4300, 4800, 5400, or 7400 lumens

Photometry

2x4 FluxGrid recessed LED, base configuration, 4200 nominal delivered lumens

LER - 124

<p>Catalog No. 2FGG42B840-4-D-UNV-DIM Test No. 36564 S/MH 1.2 Lamp Type LED Lumens 4212 Input Watts 34</p> <p>Comparative yearly lighting energy cost per 1000 lumens – \$1.94 based on 3000 hrs. and \$.08 pwr KWH.</p> <p>The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.</p> <p>Photometric values based on test performed in compliance with LM-79.</p>	<p style="text-align: center;">Candlepower</p> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45</th> <th>Cross</th> <th>Back-45</th> </tr> </thead> <tbody> <tr><td>0</td><td>1567</td><td>1567</td><td>1567</td><td>1567</td></tr> <tr><td>5</td><td>1541</td><td>1556</td><td>1559</td><td>1556</td></tr> <tr><td>15</td><td>1467</td><td>1473</td><td>1476</td><td>1473</td></tr> <tr><td>25</td><td>1323</td><td>1330</td><td>1339</td><td>1330</td></tr> <tr><td>35</td><td>1124</td><td>1147</td><td>1165</td><td>1147</td></tr> <tr><td>45</td><td>896</td><td>949</td><td>978</td><td>949</td></tr> <tr><td>55</td><td>659</td><td>737</td><td>779</td><td>737</td></tr> <tr><td>65</td><td>404</td><td>534</td><td>587</td><td>534</td></tr> <tr><td>75</td><td>203</td><td>323</td><td>365</td><td>323</td></tr> <tr><td>85</td><td>43</td><td>104</td><td>108</td><td>104</td></tr> </tbody> </table>	Angle	End	45	Cross	Back-45	0	1567	1567	1567	1567	5	1541	1556	1559	1556	15	1467	1473	1476	1473	25	1323	1330	1339	1330	35	1124	1147	1165	1147	45	896	949	978	949	55	659	737	779	737	65	404	534	587	534	75	203	323	365	323	85	43	104	108	104	<p>Light Distribution</p> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>1176</td><td>27.9</td></tr> <tr><td>0-40</td><td>1893</td><td>44.9</td></tr> <tr><td>0-60</td><td>3273</td><td>77.6</td></tr> <tr><td>0-90</td><td>4215</td><td>100</td></tr> <tr><td>0-180</td><td>4216</td><td>100</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1176	27.9	0-40	1893	44.9	0-60	3273	77.6	0-90	4215	100	0-180	4216	100	<p>Average Luminance</p> <table border="1"> <thead> <tr> <th>Zone</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>8102</td><td>8584</td><td>8845</td></tr> <tr><td>55</td><td>7349</td><td>8219</td><td>8685</td></tr> <tr><td>65</td><td>6120</td><td>8077</td><td>8890</td></tr> <tr><td>75</td><td>5025</td><td>7991</td><td>9014</td></tr> <tr><td>85</td><td>3186</td><td>7597</td><td>7905</td></tr> </tbody> </table>	Zone	End	45°	Cross	45	8102	8584	8845	55	7349	8219	8685	65	6120	8077	8890	75	5025	7991	9014	85	3186	7597	7905																																																																																					
Angle	End	45	Cross	Back-45																																																																																																																																																																																					
0	1567	1567	1567	1567																																																																																																																																																																																					
5	1541	1556	1559	1556																																																																																																																																																																																					
15	1467	1473	1476	1473																																																																																																																																																																																					
25	1323	1330	1339	1330																																																																																																																																																																																					
35	1124	1147	1165	1147																																																																																																																																																																																					
45	896	949	978	949																																																																																																																																																																																					
55	659	737	779	737																																																																																																																																																																																					
65	404	534	587	534																																																																																																																																																																																					
75	203	323	365	323																																																																																																																																																																																					
85	43	104	108	104																																																																																																																																																																																					
Degrees	Lumens	% Luminaire																																																																																																																																																																																							
0-30	1176	27.9																																																																																																																																																																																							
0-40	1893	44.9																																																																																																																																																																																							
0-60	3273	77.6																																																																																																																																																																																							
0-90	4215	100																																																																																																																																																																																							
0-180	4216	100																																																																																																																																																																																							
Zone	End	45°	Cross																																																																																																																																																																																						
45	8102	8584	8845																																																																																																																																																																																						
55	7349	8219	8685																																																																																																																																																																																						
65	6120	8077	8890																																																																																																																																																																																						
75	5025	7991	9014																																																																																																																																																																																						
85	3186	7597	7905																																																																																																																																																																																						
		<p>Coefficients of Utilization</p> <p>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</p> <table border="1"> <thead> <tr> <th>pfc =</th> <th colspan="3">20</th> <th colspan="3">80</th> <th colspan="3">70</th> <th colspan="3">50</th> </tr> <tr> <th>Ceil</th> <th colspan="3"></th> <th colspan="3"></th> <th colspan="3"></th> <th colspan="3"></th> </tr> <tr> <th>Wall</th> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> </tr> <tr> <th>RCR</th> <th colspan="12"></th> </tr> </thead> <tbody> <tr><td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td><td>111</td><td>111</td><td>111</td></tr> <tr><td>1</td><td>108</td><td>103</td><td>98</td><td>106</td><td>101</td><td>96</td><td>96</td><td>96</td><td>93</td><td>93</td><td>93</td></tr> <tr><td>2</td><td>97</td><td>90</td><td>82</td><td>95</td><td>88</td><td>81</td><td>84</td><td>79</td><td>84</td><td>79</td><td>79</td></tr> <tr><td>3</td><td>90</td><td>79</td><td>70</td><td>86</td><td>77</td><td>69</td><td>73</td><td>68</td><td>73</td><td>68</td><td>68</td></tr> <tr><td>4</td><td>81</td><td>69</td><td>60</td><td>80</td><td>68</td><td>59</td><td>66</td><td>58</td><td>66</td><td>58</td><td>58</td></tr> <tr><td>5</td><td>76</td><td>63</td><td>54</td><td>72</td><td>60</td><td>53</td><td>58</td><td>52</td><td>58</td><td>52</td><td>52</td></tr> <tr><td>6</td><td>69</td><td>56</td><td>46</td><td>68</td><td>55</td><td>46</td><td>54</td><td>46</td><td>54</td><td>46</td><td>46</td></tr> <tr><td>7</td><td>65</td><td>51</td><td>41</td><td>63</td><td>50</td><td>41</td><td>48</td><td>40</td><td>48</td><td>40</td><td>40</td></tr> <tr><td>8</td><td>59</td><td>46</td><td>38</td><td>58</td><td>46</td><td>38</td><td>45</td><td>36</td><td>45</td><td>36</td><td>36</td></tr> <tr><td>9</td><td>56</td><td>42</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>34</td><td>40</td><td>34</td><td>34</td></tr> <tr><td>10</td><td>53</td><td>40</td><td>32</td><td>52</td><td>39</td><td>32</td><td>38</td><td>30</td><td>38</td><td>30</td><td>30</td></tr> </tbody> </table>	pfc =	20			80			70			50			Ceil													Wall	70	50	30	70	50	30	50	30	70	50	30	RCR													0	118	118	118	115	115	115	111	111	111	111	111	1	108	103	98	106	101	96	96	96	93	93	93	2	97	90	82	95	88	81	84	79	84	79	79	3	90	79	70	86	77	69	73	68	73	68	68	4	81	69	60	80	68	59	66	58	66	58	58	5	76	63	54	72	60	53	58	52	58	52	52	6	69	56	46	68	55	46	54	46	54	46	46	7	65	51	41	63	50	41	48	40	48	40	40	8	59	46	38	58	46	38	45	36	45	36	36	9	56	42	34	55	41	34	40	34	40	34	34	10	53	40	32	52	39	32	38	30	38	30	30
pfc =	20			80			70			50																																																																																																																																																																															
Ceil																																																																																																																																																																																									
Wall	70	50	30	70	50	30	50	30	70	50	30																																																																																																																																																																														
RCR																																																																																																																																																																																									
0	118	118	118	115	115	115	111	111	111	111	111																																																																																																																																																																														
1	108	103	98	106	101	96	96	96	93	93	93																																																																																																																																																																														
2	97	90	82	95	88	81	84	79	84	79	79																																																																																																																																																																														
3	90	79	70	86	77	69	73	68	73	68	68																																																																																																																																																																														
4	81	69	60	80	68	59	66	58	66	58	58																																																																																																																																																																														
5	76	63	54	72	60	53	58	52	58	52	52																																																																																																																																																																														
6	69	56	46	68	55	46	54	46	54	46	46																																																																																																																																																																														
7	65	51	41	63	50	41	48	40	48	40	40																																																																																																																																																																														
8	59	46	38	58	46	38	45	36	45	36	36																																																																																																																																																																														
9	56	42	34	55	41	34	40	34	40	34	34																																																																																																																																																																														
10	53	40	32	52	39	32	38	30	38	30	30																																																																																																																																																																														

2x4 FluxGrid recessed LED, standard configuration, 4300 nominal delivered lumens

LER - 119

<p>Catalog No. 2FGG43L840-4-D-UNV-DIM Test No. 36563 S/MH 1.2 Lamp Type LED Lumens 4318 Input Watts 36</p> <p>Comparative yearly lighting energy cost per 1000 lumens – \$2.02 based on 3000 hrs. and \$.08 pwr KWH.</p> <p>The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.</p> <p>Photometric values based on test performed in compliance with LM-79.</p>	<p style="text-align: center;">Candlepower</p> <table border="1"> <thead> <tr> <th>Angle</th> <th>End</th> <th>45</th> <th>Cross</th> <th>Back-45</th> </tr> </thead> <tbody> <tr><td>0</td><td>1613</td><td>1613</td><td>1613</td><td>1613</td></tr> <tr><td>5</td><td>1587</td><td>1602</td><td>1604</td><td>1602</td></tr> <tr><td>15</td><td>1511</td><td>1517</td><td>1520</td><td>1517</td></tr> <tr><td>25</td><td>1362</td><td>1369</td><td>1380</td><td>1369</td></tr> <tr><td>35</td><td>1157</td><td>1182</td><td>1199</td><td>1182</td></tr> <tr><td>45</td><td>922</td><td>978</td><td>1006</td><td>978</td></tr> <tr><td>55</td><td>679</td><td>759</td><td>800</td><td>759</td></tr> <tr><td>65</td><td>416</td><td>514</td><td>605</td><td>514</td></tr> <tr><td>75</td><td>209</td><td>332</td><td>377</td><td>332</td></tr> <tr><td>85</td><td>44</td><td>106</td><td>111</td><td>106</td></tr> </tbody> </table>	Angle	End	45	Cross	Back-45	0	1613	1613	1613	1613	5	1587	1602	1604	1602	15	1511	1517	1520	1517	25	1362	1369	1380	1369	35	1157	1182	1199	1182	45	922	978	1006	978	55	679	759	800	759	65	416	514	605	514	75	209	332	377	332	85	44	106	111	106	<p>Light Distribution</p> <table border="1"> <thead> <tr> <th>Degrees</th> <th>Lumens</th> <th>% Luminaire</th> </tr> </thead> <tbody> <tr><td>0-30</td><td>1210</td><td>28.0</td></tr> <tr><td>0-40</td><td>1948</td><td>45.1</td></tr> <tr><td>0-60</td><td>3367</td><td>77.9</td></tr> <tr><td>0-90</td><td>4320</td><td>100</td></tr> <tr><td>0-180</td><td>4321</td><td>100</td></tr> </tbody> </table>	Degrees	Lumens	% Luminaire	0-30	1210	28.0	0-40	1948	45.1	0-60	3367	77.9	0-90	4320	100	0-180	4321	100	<p>Average Luminance</p> <table border="1"> <thead> <tr> <th>Zone</th> <th>End</th> <th>45°</th> <th>Cross</th> </tr> </thead> <tbody> <tr><td>45</td><td>8341</td><td>8843</td><td>9099</td></tr> <tr><td>55</td><td>7569</td><td>8460</td><td>8924</td></tr> <tr><td>65</td><td>6302</td><td>7782</td><td>9152</td></tr> <tr><td>75</td><td>5161</td><td>8208</td><td>9321</td></tr> <tr><td>85</td><td>3259</td><td>7773</td><td>8155</td></tr> </tbody> </table>	Zone	End	45°	Cross	45	8341	8843	9099	55	7569	8460	8924	65	6302	7782	9152	75	5161	8208	9321	85	3259	7773	8155																																																																																					
Angle	End	45	Cross	Back-45																																																																																																																																																																																					
0	1613	1613	1613	1613																																																																																																																																																																																					
5	1587	1602	1604	1602																																																																																																																																																																																					
15	1511	1517	1520	1517																																																																																																																																																																																					
25	1362	1369	1380	1369																																																																																																																																																																																					
35	1157	1182	1199	1182																																																																																																																																																																																					
45	922	978	1006	978																																																																																																																																																																																					
55	679	759	800	759																																																																																																																																																																																					
65	416	514	605	514																																																																																																																																																																																					
75	209	332	377	332																																																																																																																																																																																					
85	44	106	111	106																																																																																																																																																																																					
Degrees	Lumens	% Luminaire																																																																																																																																																																																							
0-30	1210	28.0																																																																																																																																																																																							
0-40	1948	45.1																																																																																																																																																																																							
0-60	3367	77.9																																																																																																																																																																																							
0-90	4320	100																																																																																																																																																																																							
0-180	4321	100																																																																																																																																																																																							
Zone	End	45°	Cross																																																																																																																																																																																						
45	8341	8843	9099																																																																																																																																																																																						
55	7569	8460	8924																																																																																																																																																																																						
65	6302	7782	9152																																																																																																																																																																																						
75	5161	8208	9321																																																																																																																																																																																						
85	3259	7773	8155																																																																																																																																																																																						
		<p>Coefficients of Utilization</p> <p>EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)</p> <table border="1"> <thead> <tr> <th>pfc =</th> <th colspan="3">20</th> <th colspan="3">80</th> <th colspan="3">70</th> <th colspan="3">50</th> </tr> <tr> <th>Ceil</th> <th colspan="3"></th> <th colspan="3"></th> <th colspan="3"></th> <th colspan="3"></th> </tr> <tr> <th>Wall</th> <th>70</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> <th>50</th> <th>30</th> <th>70</th> <th>50</th> <th>30</th> </tr> <tr> <th>RCR</th> <th colspan="12"></th> </tr> </thead> <tbody> <tr><td>0</td><td>118</td><td>118</td><td>118</td><td>115</td><td>115</td><td>115</td><td>111</td><td>111</td><td>111</td><td>111</td><td>111</td></tr> <tr><td>1</td><td>108</td><td>103</td><td>98</td><td>106</td><td>101</td><td>96</td><td>96</td><td>96</td><td>93</td><td>93</td><td>93</td></tr> <tr><td>2</td><td>97</td><td>90</td><td>82</td><td>95</td><td>88</td><td>81</td><td>84</td><td>79</td><td>84</td><td>79</td><td>79</td></tr> <tr><td>3</td><td>90</td><td>79</td><td>70</td><td>86</td><td>78</td><td>69</td><td>75</td><td>68</td><td>73</td><td>68</td><td>68</td></tr> <tr><td>4</td><td>81</td><td>69</td><td>60</td><td>80</td><td>68</td><td>60</td><td>66</td><td>58</td><td>66</td><td>58</td><td>58</td></tr> <tr><td>5</td><td>76</td><td>63</td><td>54</td><td>73</td><td>61</td><td>53</td><td>58</td><td>52</td><td>58</td><td>52</td><td>52</td></tr> <tr><td>6</td><td>69</td><td>56</td><td>47</td><td>68</td><td>56</td><td>46</td><td>54</td><td>46</td><td>54</td><td>46</td><td>46</td></tr> <tr><td>7</td><td>65</td><td>51</td><td>42</td><td>63</td><td>51</td><td>41</td><td>48</td><td>40</td><td>48</td><td>40</td><td>40</td></tr> <tr><td>8</td><td>59</td><td>46</td><td>38</td><td>58</td><td>46</td><td>38</td><td>45</td><td>36</td><td>45</td><td>36</td><td>36</td></tr> <tr><td>9</td><td>56</td><td>42</td><td>34</td><td>55</td><td>41</td><td>34</td><td>40</td><td>34</td><td>40</td><td>34</td><td>34</td></tr> <tr><td>10</td><td>53</td><td>40</td><td>32</td><td>52</td><td>39</td><td>32</td><td>38</td><td>30</td><td>38</td><td>30</td><td>30</td></tr> </tbody> </table>	pfc =	20			80			70			50			Ceil													Wall	70	50	30	70	50	30	50	30	70	50	30	RCR													0	118	118	118	115	115	115	111	111	111	111	111	1	108	103	98	106	101	96	96	96	93	93	93	2	97	90	82	95	88	81	84	79	84	79	79	3	90	79	70	86	78	69	75	68	73	68	68	4	81	69	60	80	68	60	66	58	66	58	58	5	76	63	54	73	61	53	58	52	58	52	52	6	69	56	47	68	56	46	54	46	54	46	46	7	65	51	42	63	51	41	48	40	48	40	40	8	59	46	38	58	46	38	45	36	45	36	36	9	56	42	34	55	41	34	40	34	40	34	34	10	53	40	32	52	39	32	38	30	38	30	30
pfc =	20			80			70			50																																																																																																																																																																															
Ceil																																																																																																																																																																																									
Wall	70	50	30	70	50	30	50	30	70	50	30																																																																																																																																																																														
RCR																																																																																																																																																																																									
0	118	118	118	115	115	115	111	111	111	111	111																																																																																																																																																																														
1	108	103	98	106	101	96	96	96	93	93	93																																																																																																																																																																														
2	97	90	82	95	88	81	84	79	84	79	79																																																																																																																																																																														
3	90	79	70	86	78	69	75	68	73	68	68																																																																																																																																																																														
4	81	69	60	80	68	60	66	58	66	58	58																																																																																																																																																																														
5	76	63	54	73	61	53	58	52	58	52	52																																																																																																																																																																														
6	69	56	47	68	56	46	54	46	54	46	46																																																																																																																																																																														
7	65	51	42	63	51	41	48	40	48	40	40																																																																																																																																																																														
8	59	46	38	58	46	38	45	36	45	36	36																																																																																																																																																																														
9	56	42	34	55	41	34	40	34	40	34	34																																																																																																																																																																														
10	53	40	32	52	39	32	38	30	38	30	30																																																																																																																																																																														

© 2018 Signify Holding. All rights reserved. Signify reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation
 200 Franklin Square Drive, Somerset, NJ 08873
 Tel. 855-486-2216

Philips Lighting Canada Ltd.
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3
 Tel. 800-668-9008