



LED BR30

7.2BR30/PER/950/P/E26/DIM 6/1FB T20

Philips BR30 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

Product data

General Information		Starting Time (Nom)		0.5 s
Base	E26 [Single Contact Medium Screw]	Warm Up Time to 60% Light (Nom)		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)		0.7
Nominal Lifetime (Nom)	15000 h	Voltage (Nom)		120 V
Switching Cycle	50000X	Temperature		
Technical Type	7.2-65W	T-Case Maximum (Nom)		70 °C
Light Technical		Controls and Dimming		
Color Code	950 [CCT of 5000K]	Dimmable		Yes
Beam Angle (Nom)	110 °	Mechanical and Housing		
Initial lumen (Nom)	650 lm	Bulb Finish		Frosted
Color Designation	Daylight	Approval and Application		
Correlated Color Temperature (Nom)	5000 K	Energy Efficiency Label (EEL)		Not applicable
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Energy Consumption kWh/1000 h		- kWh
Color Consistency	<4	Product Data		
Color Rendering Index (Nom)	90	Order product name		7.2BR30/PER/950/P/E26/DIM 6/1FB T20
LLMF At End Of Nominal Lifetime (Nom)	70 %	EAN/UPC - Product		046677548100
Operating and Electrical		Order code		548107
Input Frequency	60 Hz	Numerator - Quantity Per Pack		1
Power (Rated) (Nom)	7.2 W			
Lamp Current (Nom)	82 mA			
Wattage Equivalent	65 W			

LED BR30


Numerator - Packs per outer box	6
Material Nr. (12NC)	929002204163
Net Weight (Piece)	0.095 kg

Dimensional drawing

Product	D	C
7.2BR30/PER/950/P/E26/DIM 6/1FB T20	95 mm	132 mm

BR30 7.2-65W 650lm 5000K E26 D

Photometric data




LED BR30

Lifetime



15K LED



15K LMP

