



Representative Image

Catalog No. SGDA32AT0400

Description: 400A 3 POLE C/B ASM

UPC No 783164211634

Products > Circuit Breakers > Molded Case Circuit Breakers > Spectra RMS™ Electronic Trip

Spectra RMS Molded Case Circuit Breakers (SE150, SF250, SG600 and SK1200) have a digital, solid state, RMS sensing trip system with field installable, front-mounted rating plugs to establish or change the breaker ampere rating. Adjustable instantaneous with tracking short-time is standard on all frames. The trip system uses digital sampling to determine the RMS value of sinusoidal and non-sinusoidal currents.

Descriptors

Category	Spectra RMS™ Electronic Trip
GO Schedule	ES

Specifications

Product Line	Spectra RMS - Standard
Trip Style	Interchangeable
Frame Type	SG600
Amperage	125 A, 150 A, 175 A, 200 A, 225 A, 250 A, 300 A, 350 A, 400 A
Poles	3
System Voltage	120 Vac, 120/240 Vac, 240 Vac
120 Vac Interrupting Rating	65 KAIC
120/240 Vac Interrupting Rating	65 KAIC
240 Vac Interrupting Rating	65 KAIC
Trip Function	LSI
Continuous Current Rated	Standard
Suitable for Reverse Feed	Yes
Lugs	TCLK365
Long Time	Fixed
Short Time	Adjustable
Instantaneous	Adjustable
Current Metering	No
Protective Relays	No
Special Markings	HACR
GSA Compliance	No

Classifications

UL File #	E11592
CSA File#	LR40350

Publications

Title	Publication No.	Publication Type
Spectra RMS MCCB, Type SG600, Drawing 1-Page, Fully dimensioned outline drawing in .dxf format	GEM-2879-DXF	Drawings-Outline and Dimensional
Spectra RMS MCCB, Type SG600, Drawing 1-Page, Fully dimensioned outline drawing in .pdf format	GEM-2879-PDF	Drawings-Outline and Dimensional
SG (400/600AF); Let-Through Energy 1-page let-through energy curve.	K215-198B	Time Current Curves
SG (400/600AF); Peak Let-Through Current 1-page peak let through current curve.	K215-199B	Time Current Curves
Spectra RMS MCCB, Type SG600, Model Full Scale solid model in .stp format for SG600 Circuit Breakers.	GEM-2879-STP	Drawings-Outline and Dimensional
SG (400AF); Long/Tracking Short Time Instantaneous 1-page time current curve.	K215-174B	Time Current Curves

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.