

TORK[®]

nsi
INDUSTRIES

SPECIFICATION SHEET

Project Info:	Type:
Job Ref:	Catalog Number:
Approvals:	Date:

ZS124 ELECTRONIC SERIES

Electronic Instant Response LED Photocontrol



APPLICATIONS & FEATURES

- All LED, CFL, Induction, HPS and HID lighting fixtures requiring instant response dust-to-dawn control.
- Flood Lamp.
- Patio Lamp.
- Decorative Lighting.
- Long-life Zero-Cross Technology.
- Filtered IR non-drifting silicon sensor designed for human eye response.
- Coated circuit board for extreme weather and moisture protection.
- 15,000 cycles, 20-year design life.
- 12" wire leads 18 AWG.

SPECIFICATIONS

- Voltage: 105-305VAC, 50/60Hz.
- Tungsten: 1000 Watts.
- Ballast: 1800VA (US) or 1000VA (Canada).
- LED Electronic Ballast: 8A or Totaling 2220W@277VAC.
- Dielectric Strength: 5000VAC.
- Turn ON Light Level: 1.5fc Instant.
- Turn OFF light Level: 1.5:1(2.25fc) with 2-5 second delay.
- Operating Temperature: -40° to 158°F (-40°C to -70°C).
- Fail Mode: On.
- Surge Protection: 445 Joule MOV.
- Power Consumption: <.5Watts.



ZS124
Electronic LED Photocontrol Fixed Position

DIMENSIONS

REGULATORY LISTINGS

- ANSI C136.10-2010
- UL773 & CSA TIL A15



LIMITED WARRANTY

- 10-year manufacturer's warranty