



Core & Coil (71A) MH ~LT~ 175W

CORE & COIL HID 71A5337500DBP

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	M90-M140
Lamp Type	100W MH
Number of Lamps	1 piece/unit
Circuit Type	R-HPF
Ballast Type	Magnetic HID
Base Model	71A5337BP
Core Size	2 5/8 x 2 3/16
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	INTEGRAL
Ignitor Temperature Rating	125°C
Capacitor Value	10 MFD
Capacitor Catalog Number	7C100M30RA
Capacitor Requirements	280V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.65 in
Capacitor Height	2.75 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	277 V


Input Frequency	60 Hz
Input Current (Open Circuit)	1.05 A
Input Current (Starting)	0.7 A
Input Current (Short Circuit)	0.25-0.35 A
Secondary Short Circuit Current	1.05-1.55 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Open Circuit Voltage	277 V
Input Current (Nom)	0.45 A A
Input Power (Nom)	118 W
Rated Lamp Power	100 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	2'
Recommended Fuse Value	3 A

Core & Coil (71A) MH ~LT~ 175W

Approval and Application	
Open Circuit Voltage Test (Volts)	260-290 V
Approval Marks	RoHS Compliant CSA certificate
Temperature Marking	A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

Product Data	
Order product name	CORE & COIL HID 71A5337500DBP
EAN/UPC - Product	781087097625
Order code	913700532209
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	913700532209
Net Weight (Piece)	1.411 kg

Dimensional drawing



MH BAL 100W M90/140 277V C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5337500DBP	3.1 in	1.8 in	2.6 in	2.2 in	2.2 in	1.8 in

