


# Telecom Main Grounding Busbar – TMGBA20L27PT



- Meets TIA-607-C and conforms to BICSI® recommendations
- Complies with NEMA® standards
- Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)
- Telecom grounding busbar splice kits are available to extend the length of the busbar



Part Number	TMGBA20L27PT
Material	Copper
Tin Plating	Yes
Width (W)	101.6 mm
Thickness (T)	6.35 mm
Length 1 (L1)	508 mm
Length 2 (L2)	229 mm
Hole Size 1 (HS1)	5/16"
Hole Size 1 Number of Pairs	27
Hole Size 2 (HS2)	7/16"
Hole Size 2 Number of Pairs	3
A	25.4 mm
B	28.6 mm
C	15.9 mm
D	15.9 mm
Certifications	cULus
Standard Packaging Quantity	1 pc
UPC	78285644557
EAN-13	0782856445579

BICSI is a registered service mark of Building Industry Consulting Service International, Inc. NEMA is a registered service mark of National Electrical Manufacturers Association. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2019 nVent All rights reserved

nVent, nVent CADDY, nVent ERICO, nVent ERIFLEX and nVent LENTON are owned by nVent or its global affiliates.

All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.