



This economical linear high-bay delivers versatility and ultra-high efficiency. Available in 90, 125, 175 and 260 Watt versions for mounting heights ranging from 15 to 50 feet.

Color: White

Weight: 17.5 lbs

| | |
|---------------------|--------------|
| Project: | Type: |
| Prepared By: | Date: |

| Driver Info | | LED Info | |
|--------------|------------------|-----------------|-----------------|
| Type: | Constant Current | Watts: | 125W |
| 120V: | 1.09A | Color Temp: | 4000K (Neutral) |
| 208V: | 0.65A | Color Accuracy: | 84 CRI |
| 240V: | 0.56A | L70 Lifespan: | 50,000 |
| 277V: | 0.46A | Lumens: | 17,441 |
| Input Watts: | 129W | Efficacy: | 135 LPW |
| Efficiency: | 97% | | |

Technical Specifications

Listings

UL Listed:

Suitable for damp locations

DLC Listed:

This product is listed by Design Lights Consortium (DLC) as an ultra-efficient premium product that qualifies for the highest tier of rebates from DLC Member Utilities.

DLC Product Code: PGAW7XBQ

IESNA LM-79 & LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

LED Characteristics

Lifespan:

50,000-hour LED lifespan based on IES LM-80 results and TM-21 calculations

LEDs:

Long-life, high-efficiency, surface mount LEDs

Color Stability:

LED color temperature is warranted to shift no more than 200K in CCT over a 5 year period

Color Uniformity:

RAB's range of CCT (Correlated Color Temperature) follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

Electrical

Driver:

Constant Current, Class 2, 120-277V, 50/60Hz, 120V: 1.09A, 208V: 0.65A, 240V: 0.56A, 277V 0.46A

Dimming Driver:

Driver includes dimming control wiring for 0-10V dimming systems. Requires separate 0-10V DC dimming circuit. Dims as low as 10%.

THD:

7.6% at 120V, 8.1% at 277V

Power Factor:

99.5% at 120V, 96.5% at 277V

Surge Protection:

4kV

Construction

Operating Temperature:

-20°C (-4°F) - 55°C (131°F)

Housing:

Die formed painted steel

Lens:

Diffused Polymethyl Methacrylate (PMMA)

Mounting:

V hooks and optional pendant mounting. AEROBAY™ comes with two 42" chains.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color

Green Technology:

Mercury and UV-free. RoHS compliant components.

Other

Replacement:

125W replaces up to (6) F32T8, (4) F54T5 or 400W HID

LOSBAY800 Sensor:

360° White Lens (Installed) - 60 ft. diameter when mounted at 40 ft., Aisle Black Lens (included as option) - 60 ft. x 20 ft. wide.




5 Yr Limited Warranty:

The RAB 5-year, limited warranty covers light output, driver performance and paint finish. RAB's warranty is subject to all terms and conditions found at

Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Dimensions



Features

- High efficiency. Low price.
- Available with factory-installed Lightcloud controls
- Ideal for industrial warehouse spaces
- 50,000 hour LED lifespan
- 5-Year, Limited Warranty

Ordering Matrix

| Family | Length | Wattage | Color Temp | Voltage | Control Options | Battery Backup | Cord & Plug |
|--------|-----------|------------|----------------------|------------------|----------------------------------|---------------------------|------------------------------------------|
| ARBAY | 2 | 125 | N | ^ | /LOS | ^ | ^ |
| | 2 = 2 ft. | 90 = 90W | Blank = 5000K (Cool) | Blank = 120-277V | Blank = No Control Option | Blank = No Battery Backup | Blank = No cord and plug |
| | 4 = 4 ft. | 125 = 125W | N = 4000K (Neutral) | /480 = 480V | /LCS = LCHBSENSE w/ mounting arm | /E2 = Battery Backup | /8C = 8 ft. cord, no plug |
| | | 175 = 175W | | | /LOS = LOSBAY800 w/ mounting arm | | /8CP = 8 ft. cord & straight plug, 120V |
| | | 260 = 260W | | | /LC = Lightcloud | | /8CP2 = 8 ft. cord & straight plug, 277V |
| | | | | | | | /8CPT2 = 8 ft. cord & Twistlock, 277V |
| | | | | | | | /8CPT4 = 8 ft. cord & Twistlock, 480V |