DESCRIPTION:

SNAPNRACK, STANDARD RAIL SPLICE

PART NUMBER(S):

242-04014, 242-04015

DRAWN BY:

M.Watkins


**REVISION:** 

A

Solar Mounting Solutions

595 MARKET STREET, 29TH FLOOR • SAN FRANCISCO, CA 94105 USA PHONE (415) 580-6900 • FAX (415) 580-6902

THE INFORMATION IN THIS DRAWING IS CONFIDENTIAL AND PROPRIETARY. ANY REPRODUCTION, DISCLOSURE, OR USE THEREOF IS PROHIBITED WITHOUT THE WRITTEN CONSENT OF SUNRUN SOUTH LLC.



PARTS LIST				
ITEM	QTY	DESCRIPTION		
1	1	SNAPNRACK, STANDARD RAIL SPLICE BASE, CLEAR / BLACK		
2	3	BOLT, HEX CAP, 5/16IN-18 X 1IN, SS		
3	3	5/16IN SS SPLIT LOCK WASHER		
4	1	SNAPNRACK, BONDING STANDARD RAIL SPLICE INSERT, MILL		

MATERIALS:	6000 SERIES ALUMINUM, STAINLESS STEEL	OPTIONS:
DESIGN LOAD (LBS):	N/A	CLEAR / BLACK ANODIZED
ULTIMATE LOAD (LBS):	N/A	
TORQUE SPECIFICATION:	10+ LB-FT	
CERTIFICATION:	UL 2703, FILE E359313	
WEIGHT (LBS):	0.69	

**DESCRIPTION:** 

PART NUMBER(S):

SNAPNRACK, STANDARD RAIL SPLICE

242-04014, 242-04015

M.Watkins


DRAWN BY:


REVISION:

A

595 MARKET STREET, 29TH FLOOR • SAN FRANCISCO, CA 94105 USA PHONE (415) 580-6900 • FAX (415) 580-6902

THE INFORMATION IN THIS DRAWING IS CONFIDENTIAL AND PROPRIETARY. ANY REPRODUCTION, DISCLOSURE, OR USE THEREOF IS PROHIBITED WITHOUT THE WRITTEN CONSENT OF SUNRUN SOUTH LLC.





VIEW A-A SCALE 1:1