




SCREW:N/A	MATERIAL: L172025SH, CDA-122 CU	CELL: CSP	TOLERANCES-UNLESS OTHERWISE SPECIFIED		DWG. NO.	Y1511-S	SHEET 1 OF 1	
CAT. NO.:SEE CHART	PLATING:EL-TIN	STUFFER SHT.:FORM 157	2 PL. DEC. ±.015	TRUE C.L. ±.015				
MASS:SEE CHART	MARKING: SEE CHART		3 PL. DEC. ±.015	ANGLES ±1	DATE:7/5/2007	SCALE: NTS		
SURFACE AREA:						SIZE: B		

REV.	DESCRIPTION
G	





DETAIL A
TOP AND BOTTOM INK MARKINGS ARE IDENTICAL
INK COLOR:BROWN
PER SPEC #: F921

CAT #: SEE CHART BELOW



VIEW15
SCALE 1 : 1



Part Number	Catalog Number	"A"	"B"	"C"	"D"	"G"	SAWCUT LENGTH	TANG MARKING
Y1511C36T	CSWS-500-14	2.907	0.875	0.000	0.281	0.180	3.157	
Y1511C47T	CSWS-500-516	2.907	0.875	0.000	0.343	0.180	3.157	ILSCO, CSWS-500-516, 5/16, 500 kcmil, 350/373 FLEX, DIE 87, UL, CSA
Y1511C46T	CSWS-500-38	2.907	0.875	0.000	0.406	0.211	3.157	ILSCO, CSWS-500-38, DIE 87, 500 kcmil, 350/373 FLEX, UL, CSA
Y1511C42T	CSWS-500-12	3.282	1.250	0.000	0.562	0.265	3.532	ILSCO, CSWS-500-12, 1/2, 500 kcmil, 350/373 FLEX, DIE 87, UL, CSA
Y1511C43T	CSWS-500-58	3.469	1.437	0.000	0.656	0.343	3.719	ILSCO, CSWS-500-58, DIE 87, 500 kcmil, 350/373 FLEX, UL, CSA
Y1511C44T	CSWS-500-34	3.719	1.687	0.000	0.781	0.359	3.969	
Y1511C45T	CSWS-500-78	3.969	1.937	0.000	0.906	0.437	4.219	
Y1511C75T	CSWS-500-1	4.157	2.125	0.000	1.031	0.500	4.407	

THE INFORMATION CONTAINED WITHIN THIS DOCUMENT IS PROPRIETARY TO ILSCO AND MAY NOT BE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT