

Part Number: 29524C



VFD, 3+3G(Segmented) C #8+3 of #14 Str BC, XLPO Ins M4, CTS, Blk PVC Jkt, 600V TC-ER 90C Dry/Wet 1000V CSA AWM I/II A/B

 [Request Sample](#)

Product Description

Belden Construction Grade VFD Cables with Dual Copper Tape Shield, 3+3G(Segmented) Conductor 8+3 of 14AWG (7x16) Bare Copper, XLPO Insulation M4 Color Code, Overall Dual Copper Tapes Helically Applied Shield, Black PVC Outer Jacket, 600V TC-ER 90C Dry/Wet 1000V CSA AWM I/II A/B SUN RES DIR BUR

Technical Specifications

Product Overview

Suitable Applications:	AC Motor drives, VFD, Variable Frequency drives
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
	8	7x16	BC - Bare Copper	3
Ground Wire	14	7x22	BC - Bare Copper	3

Conductor Count:	3
Conductor Size:	8 AWG

Insulation

Material	Nominal Wall Thickness
XLPE - Cross Linked Polyethylene	0.046 in

Color Chart

Number	Color
1	Black and Numbered 1
2	Black and Numbered 2
3	Black and Numbered 3

Outer Shield Material

Type	Layer	Material	Coverage [%]
Tape	1	Spiral Copper	100 %
Tape	2	Spiral Copper	100 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.646 in	0.060 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
0.64 Ohm/1000ft

Current

Max. Recommended Current [A]
55 Amps per conductor @ 25°C

Voltage

Description	UL Description	UL Voltage Rating	Voltage Rating [V]
CSA AWM I/II A/B	NEC Type TC	600 V RMS (NEC Type TC)	1000 V RMS (CSA AWM I/II A/B)

Temperature Range

UL Temp Rating:	90°C Wet/Dry
Operating Temp Range:	-40°C To +90°C Wet/Dry

Mechanical Characteristics

Bulk Cable Weight:	340 lbs/1000ft
Max Recommended Pulling Tension:	576 lbs
Min Bend Radius/Minor Axis:	6.5 in

Standards

NEC Articles:	336 - ER
NEC/(UL) Specification:	TC-ER, XHHW-2 Singles
CSA AWM Specification:	1000 V AWM I/II A/B
PMSHA Specification:	P-07-KA070003

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2007-08-17
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT4
IEEE Flammability:	1202, 383 Vertical Tray Flame Test (70,000 BTU)
UL voltage rating:	600 V RMS (NEC Type TC)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color
29524C 0105000	Black

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.