


ADVANCED CABLE TIES PART NUMBER	BUNDLE DIAMETER		A	B	C	D	E	F	MIN LOOP TENSILE LBS (n)	ANSI/UL 94 MH FLAMABILITY RATING	PLENUM RATING
	MIN IN (mm)	MAX IN (mm)	IN (mm) +/- .125 (3.175mm)	IN (mm) +/- .005 (.127mm)	IN (mm) +/- .005 (.127mm)	IN (mm) +/- .020 (.508mm)	IN (mm) +/- .020 (.508mm)	IN (mm) +/- .030 (.762mm)			
AP(R, L)-07-50-9	.06 (1.57mm)	1.87 (47.6mm)	7.562 (192.075mm)	.052 (1.320mm)	.180 (4.572mm)	.300 (7.620mm)	.215 (5.461mm)	.305 (7.747mm)	50 (222)	V-2	AH-2
AP(R, L)-07-50-0	.06 (1.57mm)	1.87 (47.6mm)	7.562 (192.075mm)	.052 (1.320mm)	.180 (4.572mm)	.300 (7.620mm)	.215 (5.461mm)	.305 (7.747mm)	50 (222)	V-2	AH-2
AP(R, L)-11-50-9	.06 (1.57mm)	3.06 (77.7mm)	11.250 (285.751mm)	.052 (1.320mm)	.180 (4.572mm)	.300 (7.620mm)	.215 (5.461mm)	.305 (7.747mm)	50 (222)	V-2	AH-2
AP(R, L)-11-50-0	.06 (1.57mm)	3.06 (77.7mm)	11.250 (285.751mm)	.052 (1.320mm)	.180 (4.572mm)	.300 (7.620mm)	.215 (5.461mm)	.305 (7.747mm)	50 (222)	V-2	AH-2
AP(R, L)-14-50-9	.06 (1.57mm)	4.00 (101.6mm)	14.500 (368.300mm)	.052 (1.320mm)	.180 (4.572mm)	.300 (7.620mm)	.215 (5.461mm)	.305 (7.747mm)	50 (222)	V-2	AH-2
AP(R, L)-14-50-0	.06 (1.57mm)	4.00 (101.6mm)	14.500 (368.300mm)	.052 (1.320mm)	.180 (4.572mm)	.300 (7.620mm)	.215 (5.461mm)	.305 (7.747mm)	50 (222)	V-2	AH-2
AP(R, L)-17-50-9	.118 (3.0mm)	5.08 (129.0mm)	17.87 (454.02mm)	.055 (1.397mm)	.185 (4.69mm)	.330 (8.382mm)	.230 (5.842mm)	.330 (8.382mm)	49 (220)	V-2	AH-2
AP(R, L)-17-50-0	.118 (3.0mm)	5.08 (129.0mm)	17.87 (454.02mm)	.055 (1.397mm)	.185 (4.69mm)	.330 (8.382mm)	.230 (5.842mm)	.330 (8.382mm)	49 (220)	V-2	AH-2
AP(R, L)-21-50-9	.118 (3.0mm)	6.30 (160.0mm)	21.62 (549.27mm)	.057 (1.447mm)	.185 (4.69mm)	.330 (8.382mm)	.233 (5.918mm)	.330 (8.382mm)	49 (220)	V-2	AH-2
AP(R, L)-21-50-0	.118 (3.0mm)	6.30 (160.0mm)	21.62 (549.27mm)	.057 (1.447mm)	.185 (4.69mm)	.330 (8.382mm)	.233 (5.918mm)	.330 (8.382mm)	49 (220)	V-2	AH-2
											
<b>ADVANCED CABLE TIES – 50 LB. (222n) STANDARD SERIES CABLE TIES</b>											
						<b>COLOR DESIGNATIONS:</b>			<b>MATERIAL:</b>		
						0 = UV BLACK    9 = NATURAL			<b>NYLON 6/6 POLYAMIDE</b>		
C	12/19/17	PB	VA	VA	UPDATED UL SPECS AND ADDED VENDOR SPECS			SHEET 1 OF 1		REV.: C	
B	4/29/17	JA	KT	KT	NEW LOGO ADDED			DRAWN BY		DATE	
A	12/22/14	JA	KT	KT	INITIAL RELEASE			CHECK		SCALE	
REV	DATE	BY	CHK	APPROVE	DESCRIPTION			JA		4/29/2017	
								KT		NONE	

CONFIDENTIAL PROPERTY OF ADVANCED CABLE TIES, INC.

THIS DRAWING IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF ADVANCED CABLE TIES, INC.