

HZ Electric Supply

February 2019 Newsletter

Now on Our Website

News

Events

New Products

Price Increases

Price Increases

Throughout February, the following vendors will be implementing price increases:

Allied Moulded
Black and Decker
B-Line
Eaton Lighting
Edwards
Eveready/Energizer
Generac
Hubbell Lighting
Lenox
Leviton
Newell Writing
Panduit
Philips Lamps
Philips Luminaires
Quazite
Satco
Siemens
World Dryer
Acuity
Klein
Carlton
Thomas & Betts
Lutron



Have you heard about our Online Resources? Our website offers you mobile tips and tools for your everyday jobs. Everything from (cross) reference lists to heat loss, volume, and square footage calculators are available to you with a few quick clicks. Simply select "Online Resources" under the "Resource" tab and you will be able to sift through different categories such as energy, power and distribution, safety and more. Each category contains links that will bring you right to the source. This way, you know that you will be directed right to the source for the most accurate information. On the job and want to double check your calculations or make sure you're working within safety codes, **Check Out our Online Resources Today!**



We are very excited for the 2019 Incentive Programs. EnergizeCT released their 2019 program at a roll-out meeting last week. Massachusetts will release theirs in February. The most lucrative incentives will be fixtures with onboard controls. We look forward to working with our customers on

making sure you have the right products to meet the new parameters that were introduced.

[Learn More about our Energy Solutions](#)

Featured Products



CPX LED Flat Panel

CPX 2X2 3200LM 35K M4

CPX 2X2 3200LM 40K M4

CPX 2X4 4000LM 35K M2

CPX 2X4 4000LM 40K M2

- Features a diffuse lens for even illumination over the surface of the panel
- Industry standard wattages
- Long-life LEDs maintain greater than 70% of their lumen output at 50,000 hours
- 0-10V dimming driver, dims to 10%
- Ideal for small offices, schools, and retail

[Click Here for More](#)



Get all of the products you need when you need them with Acuity's new Contractor Select Program. The most popular products from Juno and Lithonia Lighting have been selected and placed into stock for easy ordering every time you visit one of our branches.

Ask your sales rep what products qualify for the Contractor Select Program or [Read More About it here!](#)



LED Round Downlight


2LEDDRIVER G2 06LM 120 FRPC

- 2" Aperture recessed downlight is IC rated for insulated or non-insulated applications
- Low profile form factor allows luminaire to fit in 2x6 construction
- 50,000 hours of life
- Comparable light output up to a 75W MR16 halogen lamp
- UL and cUL listed for wet locations

[Click Here for More](#)



New Products



HALO RL4 Direct Mount

RL4069S1EWDHM

RL6069S1EWDHM

- LED Baffle-Trim Module for 4-inch aperture applications
- SeleCCTable colors 2700K, 3000K, 3500K, 4000K, & 5000K
- Requires no housing or third party junction box
- Remote enclosure may be used in direct contact with insulation
- Can be removed from below the ceiling for service or replacement

[Click Here for More Info](#)



Sign Hero 360

KT-LED21T8-48P2S-8XX-D

KT-LED42T8-96P2S-8XX-D

- Replacement for conventional T12HO and T8HO fluorescent lamps for sign applications
- 50,000+ lifetime
- Installs using existing sockets
- Over 50% more energy efficient than HO fluorescent lamps
- No external driver or power supply needed
- Single- or double-sided outdoor signage applications

[Click Here for More Info](#)



Wall Mount Luminaire

WPSLED-30 27W equivalent to 100W

MH

WPMLED-75 76W equivalent to 320W

MH

WPLLED-100 82W equivalent to 450W

MH

- Rugged die-cast aluminum construction
- Impenetrable to contaminants
- UL/cUL wet location listed
- LED driver and related electrical components are hard mounted to the die-cast housing for optimal heat sinking and operating efficiency
- Ideal for pathways, building entrances, vehicle ramps, schools, tunnels, stairways, and loading docks

[Click Here for More Info](#)



Brightness
2000
lumens



Commercial LED Strip Light

2ST1L1040R - 2 foot, 10W

2ST2L2040R - 2 foot, 19W

4ST1L2040R - 4 foot, 20W

4ST2L4040R - 4 foot, 39W

8ST2L8040R - 8 foot, 78W



SEL Emergency Light

SEL25R10SD

- EZ Hang feature facilitates fast installation



PathLinx Emergency Light

LEM4SD

- Reduces egress system cost
- Thin profile blends into the environment with expanded

- Designed to retrofit and replace fluorescent strip lights
- Surface or suspended mount capable
- Wire nuts and aligners included
- Channel knockouts (7/8") are provided for conduit installations
- Snap and lock tool-less channel cover for easy maintenance

[Click Here for More Info](#)



- Suitable for ceiling, pendant, or wall mount applications
- Provides from 25-60 feet of emergency egress coverage for a minimum of 90 min during a power outage
- Self-diagnosing
- Long-life LED source
- Poly-carbonate housing
- Remote capable options proving from 4W to 10W are available

[Click Here for More Info](#)



- egress light spacing between units
- Wide coverage pattern and RJ45 connectors allows installers to reduce the cost of equipment, materials, and labor
- External battery disconnect and easy connection features make the PathLinX LED emergency light uncomplicated and efficient throughout installation

[Click Here for More Info](#)

